

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297609

Luminaire Tested: P3AS13R50W2N902750DE010 E3DL1GPH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297609  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R50W2N902750DE010 E3DL1GPH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 428.0 lumens  
Efficiency: N/A  
Efficacy: 34.8 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297609  
CATALOG NUMBER: P3AS13R50W2N902750DE010 E3DL1GPH\_4000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1297609

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3DL1GPH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.4	13.2
10°-20°	136.4	31.9
20°-30°	133.8	31.3
30°-40°	67.4	15.7
40°-50°	21.3	5.0
50°-60°	5.5	1.3
60°-70°	3.9	0.9
70°-80°	2.4	0.6
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.6	76.3
0°-40°	394.0	92.1
0°-60°	420.9	98.3
0°-90°	428.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	428.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	621	
5°	607	56
15°	493	136
25°	297	134
35°	104	67
45°	26	21
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1297609

CATALOG NUMBER: P3AS13R50W2N902750DE010 E3DL1GPH\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	621.4
2.5°	617.6
5°	606.6
7.5°	586.8
10°	561.7
12.5°	529.3
15°	493.2
17.5°	451.3
20°	403.8
22.5°	352.4
25°	297.2
27.5°	238.6
30°	184.6
32.5°	138.9
35°	103.5
37.5°	76.5
40°	55.9
42.5°	39.6
45°	25.9
47.5°	14.8
50°	8.8
52.5°	6.5
55°	6.1
57.5°	5.3
60°	4.9
62.5°	4.6
65°	3.8
67.5°	3.4
70°	3.0
72.5°	2.7
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)