

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295650

Luminaire Tested: P3AS13R15W2N902765DE010 E3PHLD1MW\_4000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295650  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R15W2N902765DE010 E3PHLD1MW\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 90CRI ,  
E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 511.0 lumens  
Efficiency: N/A  
Efficacy: 41.5 lumens/watt  
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295650  
CATALOG NUMBER: P3AS13R15W2N902765DE010 E3PHLD1MW\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1295650

CATALOG NUMBER: P3AS13R15W2N902765DE010 E3PHLD1MW\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	95	93	92	90
2	104	98	93	89	102	97	92	88	93	89	86	90	87	84	87	85	82	87	85	82	80
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	81	77	74	72
4	92	82	76	70	90	81	75	70	79	73	69	77	72	68	75	71	67	75	71	67	66
5	86	76	69	64	84	75	68	63	73	67	63	71	66	62	70	65	62	70	65	62	60
6	81	71	63	58	79	70	63	58	68	62	58	67	61	57	65	60	57	65	60	57	55
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	61	56	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	58	53	49	47
9	69	58	51	47	68	57	51	46	56	50	46	55	50	46	54	49	46	54	49	46	44
10	65	54	48	44	64	54	48	44	53	47	43	52	47	43	52	47	43	52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	148694
5°	139401
10°	114315
15°	88809
20°	70099
25°	55866
30°	44842
35°	36594
40°	30171
45°	25367
50°	21799
55°	18848
60°	16709
65°	14528
70°	12951
75°	10421
80°	8461
85°	5535

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25367 cd/sqm



TEST NUMBER: P1295650

CATALOG NUMBER: P3AS13R15W2N902765DE010 E3PHLD1MW\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.6	11.1
10°-20°	109.6	21.4
20°-30°	106.5	20.8
30°-40°	86.1	16.8
40°-50°	63.9	12.5
50°-60°	44.6	8.7
60°-70°	28.0	5.5
70°-80°	13.3	2.6
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.7	53.4
0°-40°	358.7	70.2
0°-60°	467.3	91.4
0°-90°	511.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	511.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	678	
5°	633	57
15°	391	110
25°	231	107
35°	137	86
45°	82	64
55°	49	45
65°	28	28
75°	12	13
85°	2	2
90°	0	



TEST NUMBER: P1295650  
CATALOG NUMBER: P3AS13R15W2N902765DE010 E3PHLD1MW\_4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	678.1
2.5°	666.9
5°	633.3
7.5°	579.5
10°	513.4
12.5°	448.4
15°	391.2
17.5°	343.0
20°	300.4
22.5°	263.4
25°	230.9
27.5°	201.8
30°	177.1
32.5°	155.8
35°	136.7
37.5°	119.9
40°	105.4
42.5°	93.0
45°	81.8
47.5°	72.9
50°	63.9
52.5°	56.0
55°	49.3
57.5°	43.7
60°	38.1
62.5°	32.5
65°	28.0
67.5°	23.5
70°	20.2
72.5°	15.7
75°	12.3
77.5°	9.0
80°	6.7
82.5°	3.4
85°	2.2
87.5°	0.0
90°	0.0

(END OF REPORT)