

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295657

Luminaire Tested: P3AS13R15W2N902765DE010 E3PHLP1MW\_5000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295657  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R15W2N902765DE010 E3PHLP1MW\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 90CRI ,  
E3PHLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 359.0 lumens  
Efficiency: N/A  
Efficacy: 29.2 lumens/watt  
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295657  
CATALOG NUMBER: P3AS13R15W2N902765DE010 E3PHLP1MW\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1295657

CATALOG NUMBER: P3AS13R15W2N902765DE010 E3PHLP1MW\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	92	92	92	90
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	83	83	83	81
3	99	91	85	80	96	89	84	80	87	82	78	84	80	77	82	79	76	76	76	76	74
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	70	70	70	68
5	88	78	72	67	86	77	71	67	76	70	66	74	69	65	72	68	65	65	65	65	63
6	83	73	67	62	82	73	66	62	71	65	61	70	65	61	68	64	60	60	60	60	59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	57	57	57	55
8	75	65	59	54	74	65	58	54	63	58	54	62	57	54	61	57	53	53	53	53	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	50	50	50	49
10	69	59	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	48	48	48	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	134375
5°	123376
10°	98306
15°	73462
20°	55795
25°	42244
30°	31245
35°	22326
40°	15286
45°	10699
50°	9108
55°	8946
60°	9254
65°	9806
70°	10002
75°	10336
80°	11239
85°	11070

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 13104 cd/sqm



TEST NUMBER: P1295657

CATALOG NUMBER: P3AS13R15W2N902765DE010 E3PHLP1MW\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.6	13.8
10°-20°	90.8	25.3
20°-30°	80.4	22.4
30°-40°	52.7	14.7
40°-50°	28.2	7.8
50°-60°	21.3	5.9
60°-70°	18.3	5.1
70°-80°	12.6	3.5
80°-90°	5.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	220.8	61.5
0°-40°	273.5	76.2
0°-60°	322.9	90.0
0°-90°	359.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	359.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	613	
5°	560	50
15°	324	91
25°	175	80
35°	83	53
45°	34	28
55°	23	21
65°	19	18
75°	12	13
85°	4	5
90°	0	



TEST NUMBER: P1295657  
CATALOG NUMBER: P3AS13R15W2N902765DE010 E3PHLP1MW\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	612.8
2.5°	598.3
5°	560.5
7.5°	504.9
10°	441.5
12.5°	380.3
15°	323.6
17.5°	278.0
20°	239.1
22.5°	204.6
25°	174.6
27.5°	147.9
30°	123.4
32.5°	102.3
35°	83.4
37.5°	66.7
40°	53.4
42.5°	42.3
45°	34.5
47.5°	30.0
50°	26.7
52.5°	25.6
55°	23.4
57.5°	22.2
60°	21.1
62.5°	20.0
65°	18.9
67.5°	16.7
70°	15.6
72.5°	13.3
75°	12.2
77.5°	10.0
80°	8.9
82.5°	7.8
85°	4.4
87.5°	2.2
90°	0.0

(END OF REPORT)