

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297749

Luminaire Tested: P3AS13R50W2N902765DE010 E3D1MW\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297749  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R50W2N902765DE010 E3D1MW\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 6500K CCT AND, 90CRI ,  
E3D1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1056.0 lumens  
Efficiency: N/A  
Efficacy: 85.9 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297749  
CATALOG NUMBER: P3AS13R50W2N902765DE010 E3D1MW\_6500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1297749

CATALOG NUMBER: P3AS13R50W2N902765DE010 E3D1MW\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.0	14.6
10°-20°	389.4	36.9
20°-30°	390.0	36.9
30°-40°	109.7	10.4
40°-50°	6.6	0.6
50°-60°	2.5	0.2
60°-70°	2.0	0.2
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	933.4	88.4
0°-40°	1043.1	98.8
0°-60°	1052.2	99.6
0°-90°	1056.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1056.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1677	
5°	1641	154
15°	1401	389
25°	888	390
35°	140	110
45°	4	7
55°	3	3
65°	2	2
75°	2	1
85°	1	1
90°	0	



TEST NUMBER: P1297749  
CATALOG NUMBER: P3AS13R50W2N902765DE010 E3D1MW\_6500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1677.2
2.5°	1668.7
5°	1640.9
7.5°	1603.1
10°	1557.5
12.5°	1488.9
15°	1400.9
17.5°	1299.8
20°	1201.7
22.5°	1079.8
25°	888.4
27.5°	661.5
30°	461.6
32.5°	278.6
35°	140.5
37.5°	66.4
40°	30.9
42.5°	11.6
45°	3.9
47.5°	3.1
50°	3.1
52.5°	3.1
55°	3.1
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)