

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297756

Luminaire Tested: P3AS13R50W2N902765DE010 E3D1WMH_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50W2N902765DE010 E3D1WMH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 962.0 lumens
Efficiency: N/A
Efficacy: 78.2 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297756
CATALOG NUMBER: P3AS13R50W2N902765DE010 E3D1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1297756

CATALOG NUMBER: P3AS13R50W2N902765DE010 E3D1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	336179
5°	327228
10°	312263
15°	282703
20°	244578
25°	200624
30°	115233
35°	35790
40°	9618
45°	3380
50°	819
55°	268
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3380 cd/sqm



TEST NUMBER: P1297756

CATALOG NUMBER: P3AS13R50W2N902765DE010 E3D1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.2	14.5
10°-20°	345.0	35.9
20°-30°	362.7	37.7
30°-40°	103.8	10.8
40°-50°	10.1	1.1
50°-60°	0.8	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	846.9	88.0
0°-40°	950.7	98.8
0°-60°	961.7	100.0
0°-90°	962.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	962.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1533	
5°	1487	139
15°	1245	345
25°	829	363
35°	134	104
45°	11	10
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1297756

CATALOG NUMBER: P3AS13R50W2N902765DE010 E3D1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1533.1
1°	1530.7
2°	1523.9
3°	1514.1
4°	1500.9
5°	1486.6
6°	1471.3
7°	1455.0
8°	1439.8
9°	1422.1
10°	1402.4
11°	1379.7
12°	1353.6
13°	1321.0
14°	1285.7
15°	1245.3
16°	1202.5
17°	1161.1
18°	1118.7
19°	1081.4
20°	1048.1
21°	1016.2
22°	979.9
23°	938.1
24°	889.2
25°	829.2
26°	764.0
27°	691.4
28°	619.1
29°	541.0
30°	455.1
31°	374.7
32°	300.7
32.5°	268.5
33°	235.9
34°	180.9
35°	133.7
36°	98.1
37°	73.0
37.5°	63.1
38°	54.6
39°	42.4
40°	33.6
42.5°	19.0
45°	10.9



TEST NUMBER: P1297756
CATALOG NUMBER: P3AS13R50W2N902765DE010 E3D1WMH_2700K

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.1
50°	2.4
52.5°	1.0
55°	0.7
57.5°	0.7
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)