

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295758

Luminaire Tested: P3AS13R20W2N902750DE010 E3DLD1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20W2N902750DE010 E3DLD1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 5000K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 607.0 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295758
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLD1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295758

CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLD1MW_5000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 61.4 | 10.1 |
| 10°-20° | 145.1 | 23.9 |
| 20°-30° | 161.1 | 26.5 |
| 30°-40° | 122.9 | 20.2 |
| 40°-50° | 62.9 | 10.4 |
| 50°-60° | 25.8 | 4.3 |
| 60°-70° | 16.1 | 2.7 |
| 70°-80° | 9.0 | 1.5 |
| 80°-90° | 2.6 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 367.6 | 60.6 |
| 0°-40° | 490.5 | 80.8 |
| 0°-60° | 579.2 | 95.4 |
| 0°-90° | 607.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 607.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 685 | |
| 5° | 664 | 61 |
| 15° | 521 | 145 |
| 25° | 352 | 161 |
| 35° | 196 | 123 |
| 45° | 79 | 63 |
| 55° | 26 | 26 |
| 65° | 16 | 16 |
| 75° | 8 | 9 |
| 85° | 2 | 3 |
| 90° | 0 | |



TEST NUMBER: P1295758
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLD1MW_5000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 684.7 |
| 1° | 685.5 |
| 2° | 682.4 |
| 3° | 678.5 |
| 4° | 672.4 |
| 5° | 663.9 |
| 6° | 653.9 |
| 7° | 643.1 |
| 8° | 631.5 |
| 9° | 617.6 |
| 10° | 603.7 |
| 12.5° | 563.6 |
| 15° | 521.2 |
| 17.5° | 478.1 |
| 20° | 434.9 |
| 22.5° | 391.7 |
| 25° | 352.4 |
| 27.5° | 313.1 |
| 30° | 272.2 |
| 32.5° | 233.6 |
| 35° | 195.8 |
| 37.5° | 162.7 |
| 40° | 130.3 |
| 42.5° | 102.6 |
| 45° | 79.4 |
| 47.5° | 60.1 |
| 50° | 44.7 |
| 52.5° | 33.2 |
| 55° | 26.2 |
| 57.5° | 23.9 |
| 60° | 20.8 |
| 62.5° | 18.5 |
| 65° | 16.2 |
| 67.5° | 13.9 |
| 70° | 12.3 |
| 72.5° | 10.0 |
| 75° | 8.5 |
| 77.5° | 6.9 |
| 80° | 5.4 |
| 82.5° | 3.9 |
| 85° | 2.3 |
| 87.5° | 0.8 |
| 90° | 0.0 |

(END OF REPORT)