

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297776

Luminaire Tested: P3AS13R50W2N902765DE010 E3DL1LI_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297776
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50W2N902765DE010 E3DL1LI_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3500K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 873.1 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297776
CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DL1LI_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1297776
 CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DL1LI_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 114 | 111 | 108 | 106 | 111 | 109 | 106 | 104 | 105 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 94 | | | |
| 2 | 108 | 103 | 99 | 96 | 106 | 102 | 98 | 95 | 98 | 95 | 93 | 95 | 93 | 91 | 93 | 91 | 89 | 87 | | | |
| 3 | 103 | 97 | 92 | 88 | 101 | 95 | 91 | 87 | 93 | 89 | 86 | 90 | 87 | 84 | 88 | 85 | 83 | 82 | | | |
| 4 | 98 | 91 | 85 | 81 | 96 | 90 | 85 | 81 | 87 | 83 | 80 | 85 | 82 | 79 | 84 | 80 | 78 | 76 | | | |
| 5 | 93 | 85 | 80 | 75 | 92 | 84 | 79 | 75 | 83 | 78 | 74 | 81 | 77 | 74 | 79 | 76 | 73 | 72 | | | |
| 6 | 89 | 80 | 75 | 71 | 88 | 80 | 74 | 70 | 78 | 73 | 70 | 77 | 73 | 69 | 75 | 72 | 69 | 67 | | | |
| 7 | 85 | 76 | 70 | 66 | 84 | 75 | 70 | 66 | 74 | 69 | 66 | 73 | 69 | 65 | 72 | 68 | 65 | 64 | | | |
| 8 | 81 | 72 | 66 | 62 | 80 | 71 | 66 | 62 | 70 | 65 | 62 | 69 | 65 | 62 | 68 | 64 | 61 | 60 | | | |
| 9 | 78 | 68 | 63 | 59 | 76 | 68 | 62 | 59 | 67 | 62 | 59 | 66 | 62 | 58 | 65 | 61 | 58 | 57 | | | |
| 10 | 74 | 65 | 59 | 56 | 73 | 65 | 59 | 56 | 64 | 59 | 55 | 63 | 58 | 55 | 62 | 58 | 55 | 54 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 277938 |
| 5° | 272352 |
| 10° | 255105 |
| 15° | 228378 |
| 20° | 192190 |
| 25° | 146670 |
| 30° | 95331 |
| 35° | 56510 |
| 40° | 32661 |
| 45° | 16374 |
| 50° | 6106 |
| 55° | 4741 |
| 60° | 4429 |
| 65° | 4047 |
| 70° | 3975 |
| 75° | 3982 |
| 80° | 3915 |
| 85° | 4026 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 16374 cd/sqm



TEST NUMBER: P1297776

CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DL1LI_3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 115.1 | 13.2 |
| 10°-20° | 278.2 | 31.9 |
| 20°-30° | 272.9 | 31.3 |
| 30°-40° | 137.5 | 15.7 |
| 40°-50° | 43.5 | 5.0 |
| 50°-60° | 11.3 | 1.3 |
| 60°-70° | 8.0 | 0.9 |
| 70°-80° | 4.9 | 0.6 |
| 80°-90° | 1.7 | 0.2 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 666.2 | 76.3 |
| 0°-40° | 803.7 | 92.1 |
| 0°-60° | 858.5 | 98.3 |
| 0°-90° | 873.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 873.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1268 | |
| 5° | 1237 | 115 |
| 15° | 1006 | 278 |
| 25° | 606 | 273 |
| 35° | 211 | 137 |
| 45° | 53 | 43 |
| 55° | 12 | 11 |
| 65° | 8 | 8 |
| 75° | 5 | 5 |
| 85° | 2 | 2 |
| 90° | 0 | |



TEST NUMBER: P1297776
CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DL1LI_3500K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1267.5 |
| 2.5° | 1259.8 |
| 5° | 1237.3 |
| 7.5° | 1196.9 |
| 10° | 1145.7 |
| 12.5° | 1079.7 |
| 15° | 1006.0 |
| 17.5° | 920.6 |
| 20° | 823.6 |
| 22.5° | 718.8 |
| 25° | 606.2 |
| 27.5° | 486.7 |
| 30° | 376.5 |
| 32.5° | 283.3 |
| 35° | 211.1 |
| 37.5° | 156.0 |
| 40° | 114.1 |
| 42.5° | 80.7 |
| 45° | 52.8 |
| 47.5° | 30.3 |
| 50° | 17.9 |
| 52.5° | 13.2 |
| 55° | 12.4 |
| 57.5° | 10.9 |
| 60° | 10.1 |
| 62.5° | 9.3 |
| 65° | 7.8 |
| 67.5° | 7.0 |
| 70° | 6.2 |
| 72.5° | 5.4 |
| 75° | 4.7 |
| 77.5° | 3.9 |
| 80° | 3.1 |
| 82.5° | 2.3 |
| 85° | 1.6 |
| 87.5° | 0.8 |
| 90° | 0.0 |

(END OF REPORT)