

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295769

Luminaire Tested: P3AS13R20W2N902750DE010 E3DLP1WH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295769  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R20W2N902750DE010 E3DLP1WH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,  
E3DLP1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 717.0 lumens  
Efficiency: N/A  
Efficacy: 58.3 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295769  
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLP1WH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1295769

CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLP1WH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91	91	91	91
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87	87	87	87
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83	83	83	83
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79	79	79	79
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76	76	76	76
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73	73	73	73
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71	71	71	71
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68	68	68	68
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66	66	66	66

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	551644
5°	501451
10°	370623
15°	229264
20°	130935
25°	74738
30°	41905
35°	22807
40°	12481
45°	6884
50°	4025
55°	2906
60°	2719
65°	2491
70°	2244
75°	2372
80°	1768
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6884 cd/sqm



TEST NUMBER: P1295769

CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLP1WH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	197.3	27.5
10°-20°	281.6	39.3
20°-30°	147.0	20.5
30°-40°	56.8	7.9
40°-50°	18.4	2.6
50°-60°	7.2	1.0
60°-70°	4.8	0.7
70°-80°	2.9	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	625.9	87.3
0°-40°	682.7	95.2
0°-60°	708.4	98.8
0°-90°	717.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	717.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2516	
5°	2278	197
15°	1010	282
25°	309	147
35°	85	57
45°	22	18
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1295769  
CATALOG NUMBER: P3AS13R20W2N902750DE010 E3DLP1WH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2515.7
1°	2510.9
2°	2481.1
3°	2435.4
4°	2364.7
5°	2278.1
6°	2175.6
7°	2062.0
8°	1930.4
9°	1802.3
10°	1664.5
12.5°	1323.0
15°	1009.9
17.5°	755.7
20°	561.1
22.5°	415.6
25°	308.9
27.5°	227.9
30°	165.5
32.5°	119.8
35°	85.2
37.5°	61.6
40°	43.6
42.5°	31.2
45°	22.2
47.5°	15.9
50°	11.8
52.5°	9.0
55°	7.6
57.5°	6.9
60°	6.2
62.5°	5.5
65°	4.8
67.5°	4.2
70°	3.5
72.5°	3.5
75°	2.8
77.5°	2.1
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)