

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295808

Luminaire Tested: P3AS13R20W2N902765DE010 E3CD1MB_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295808
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20W2N902765DE010 E3CD1MB_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 965.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295808
CATALOG NUMBER: P3AS13R20W2N902765DE010 E3CD1MB_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295808

CATALOG NUMBER: P3AS13R20W2N902765DE010 E3CD1MB_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99		98
2	112	109	106	104	110	108	105	103	104	103	101	102	100	99	99	98	97		95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95		93
4	107	102	99	96	105	101	98	96	99	97	94	97	95	93	96	94	92		91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91		90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89		88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87		86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85		85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84		83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82		82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1498761
5°	1300877
10°	803793
15°	279184
20°	85734
25°	30316
30°	11217
35°	4497
40°	2405
45°	961
50°	512
55°	573
60°	658
65°	415
70°	513
75°	678
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 961 cd/sqm



TEST NUMBER: P1295808

CATALOG NUMBER: P3AS13R20W2N902765DE010 E3CD1MB_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	490.5	50.8
10°-20°	389.2	40.3
20°-30°	67.4	7.0
30°-40°	12.3	1.3
40°-50°	2.8	0.3
50°-60°	1.3	0.1
60°-70°	0.9	0.1
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	947.0	98.1
0°-40°	959.3	99.4
0°-60°	963.4	99.8
0°-90°	965.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	965.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6835	
5°	5910	490
15°	1230	389
25°	125	67
35°	17	12
45°	3	3
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1295808

CATALOG NUMBER: P3AS13R20W2N902765DE010 E3CD1MB_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	6834.9
1°	6802.0
2°	6672.2
3°	6463.6
4°	6219.2
5°	5909.9
6°	5555.4
7°	5143.0
8°	4673.2
9°	4145.4
10°	3609.9
12.5°	2277.0
15°	1229.8
17.5°	656.9
20°	367.4
22.5°	210.1
25°	125.3
27.5°	76.4
30°	44.3
32.5°	26.0
35°	16.8
37.5°	11.5
40°	8.4
42.5°	5.3
45°	3.1
47.5°	1.5
50°	1.5
52.5°	1.5
55°	1.5
57.5°	1.5
60°	1.5
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)