

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295922

Luminaire Tested: P3AS13R20W2N902765DE010 E3DLP1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295922
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20W2N902765DE010 E3DLP1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 791.0 lumens
Efficiency: N/A
Efficacy: 64.3 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295922
CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLP1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295922
 CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLP1WH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | | 0 |
| RCR | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | | 100 |
| 1 | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | | 95 |
| 2 | 110 | 106 | 102 | 100 | 108 | 104 | 101 | 98 | 101 | 98 | 96 | 98 | 96 | 94 | 95 | 94 | 92 | | 91 |
| 3 | 106 | 100 | 96 | 93 | 104 | 99 | 95 | 92 | 97 | 93 | 91 | 94 | 92 | 89 | 92 | 90 | 88 | | 87 |
| 4 | 102 | 96 | 91 | 88 | 100 | 95 | 90 | 87 | 92 | 89 | 86 | 91 | 88 | 85 | 89 | 86 | 84 | | 83 |
| 5 | 98 | 91 | 87 | 83 | 97 | 90 | 86 | 83 | 89 | 85 | 82 | 87 | 84 | 81 | 86 | 83 | 81 | | 79 |
| 6 | 95 | 87 | 83 | 79 | 93 | 87 | 82 | 79 | 85 | 81 | 78 | 84 | 81 | 78 | 83 | 80 | 77 | | 76 |
| 7 | 91 | 84 | 79 | 76 | 90 | 83 | 79 | 76 | 82 | 78 | 75 | 81 | 78 | 75 | 80 | 77 | 75 | | 73 |
| 8 | 88 | 81 | 76 | 73 | 87 | 80 | 76 | 73 | 79 | 75 | 72 | 78 | 75 | 72 | 78 | 74 | 72 | | 71 |
| 9 | 85 | 78 | 73 | 70 | 85 | 77 | 73 | 70 | 77 | 73 | 70 | 76 | 72 | 69 | 75 | 72 | 69 | | 68 |
| 10 | 83 | 75 | 71 | 68 | 82 | 75 | 70 | 67 | 74 | 70 | 67 | 73 | 70 | 67 | 73 | 69 | 67 | | 66 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 608592 |
| 5° | 553223 |
| 10° | 408855 |
| 15° | 252919 |
| 20° | 144446 |
| 25° | 82456 |
| 30° | 46235 |
| 35° | 25163 |
| 40° | 13769 |
| 45° | 7598 |
| 50° | 4435 |
| 55° | 3211 |
| 60° | 3026 |
| 65° | 2750 |
| 70° | 2436 |
| 75° | 2626 |
| 80° | 1894 |
| 85° | 2013 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7598 cd/sqm



TEST NUMBER: P1295922

CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLP1WH_3000K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 217.6 | 27.5 |
| 10°-20° | 310.7 | 39.3 |
| 20°-30° | 162.2 | 20.5 |
| 30°-40° | 62.7 | 7.9 |
| 40°-50° | 20.4 | 2.6 |
| 50°-60° | 8.0 | 1.0 |
| 60°-70° | 5.3 | 0.7 |
| 70°-80° | 3.1 | 0.4 |
| 80°-90° | 1.0 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 690.5 | 87.3 |
| 0°-40° | 753.2 | 95.2 |
| 0°-60° | 781.5 | 98.8 |
| 0°-90° | 791.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 791.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 2775 | |
| 5° | 2513 | 218 |
| 15° | 1114 | 311 |
| 25° | 341 | 162 |
| 35° | 94 | 63 |
| 45° | 24 | 20 |
| 55° | 8 | 8 |
| 65° | 5 | 5 |
| 75° | 3 | 3 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1295922
CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 2775.4 |
| 1° | 2770.0 |
| 2° | 2737.2 |
| 3° | 2686.7 |
| 4° | 2608.8 |
| 5° | 2513.3 |
| 6° | 2400.2 |
| 7° | 2274.9 |
| 8° | 2129.7 |
| 9° | 1988.3 |
| 10° | 1836.2 |
| 12.5° | 1459.5 |
| 15° | 1114.1 |
| 17.5° | 833.7 |
| 20° | 619.0 |
| 22.5° | 458.5 |
| 25° | 340.8 |
| 27.5° | 251.4 |
| 30° | 182.6 |
| 32.5° | 132.2 |
| 35° | 94.0 |
| 37.5° | 68.0 |
| 40° | 48.1 |
| 42.5° | 34.4 |
| 45° | 24.5 |
| 47.5° | 17.6 |
| 50° | 13.0 |
| 52.5° | 9.9 |
| 55° | 8.4 |
| 57.5° | 7.6 |
| 60° | 6.9 |
| 62.5° | 6.1 |
| 65° | 5.3 |
| 67.5° | 4.6 |
| 70° | 3.8 |
| 72.5° | 3.8 |
| 75° | 3.1 |
| 77.5° | 2.3 |
| 80° | 1.5 |
| 82.5° | 1.5 |
| 85° | 0.8 |
| 87.5° | 0.8 |
| 90° | 0.0 |

(END OF REPORT)