

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297920

Luminaire Tested: P3AS13R55W2N902750DE010 E3D1WMH\_2700K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297920  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R55W2N902750DE010 E3D1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,  
E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 894.0 lumens  
Efficiency: N/A  
Efficacy: 72.7 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297920  
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3D1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297920  
 CATALOG NUMBER: P3AS13R55W2N902750DE010 E3D1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     | 0  |    |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 114 | 111 | 109 | 107 | 112 | 109 | 107 | 105 | 105 | 104 | 102 | 102 | 100 | 99  | 98  | 97  | 96  | 95  |    |    |
| 2   | 109 | 105 | 101 | 98  | 107 | 103 | 100 | 97  | 100 | 97  | 95  | 97  | 95  | 93  | 94  | 92  | 91  | 89  |    |    |
| 3   | 104 | 98  | 94  | 90  | 102 | 97  | 93  | 90  | 95  | 91  | 88  | 92  | 89  | 87  | 90  | 88  | 86  | 84  |    |    |
| 4   | 100 | 93  | 88  | 84  | 98  | 92  | 87  | 84  | 90  | 86  | 83  | 88  | 84  | 82  | 86  | 83  | 81  | 79  |    |    |
| 5   | 95  | 88  | 83  | 79  | 94  | 87  | 82  | 78  | 85  | 81  | 78  | 84  | 80  | 77  | 82  | 79  | 76  | 75  |    |    |
| 6   | 91  | 83  | 78  | 74  | 90  | 82  | 77  | 74  | 81  | 76  | 73  | 80  | 76  | 73  | 78  | 75  | 72  | 71  |    |    |
| 7   | 87  | 79  | 73  | 70  | 86  | 78  | 73  | 69  | 77  | 72  | 69  | 76  | 72  | 69  | 75  | 71  | 68  | 67  |    |    |
| 8   | 83  | 75  | 69  | 66  | 82  | 74  | 69  | 66  | 73  | 69  | 65  | 72  | 68  | 65  | 71  | 68  | 65  | 63  |    |    |
| 9   | 80  | 71  | 66  | 62  | 79  | 71  | 66  | 62  | 70  | 65  | 62  | 69  | 65  | 62  | 68  | 64  | 61  | 60  |    |    |
| 10  | 77  | 68  | 62  | 59  | 76  | 67  | 62  | 59  | 67  | 62  | 59  | 66  | 62  | 59  | 65  | 61  | 58  | 57  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 259256 |
| 5°  | 250076 |
| 10° | 259024 |
| 15° | 255370 |
| 20° | 236341 |
| 25° | 191140 |
| 30° | 114549 |
| 35° | 38815  |
| 40° | 10706  |
| 45° | 4745   |
| 50° | 1399   |
| 55° | 268    |
| 60° | 132    |
| 65° | 156    |
| 70° | 192    |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 4745 cd/sqm



TEST NUMBER: P1297920

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3D1WMH\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 109.9  | 12.3      |
| 10°-20°   | 313.2  | 35.0      |
| 20°-30°   | 348.1  | 38.9      |
| 30°-40°   | 108.4  | 12.1      |
| 40°-50°   | 13.0   | 1.5       |
| 50°-60°   | 1.0    | 0.1       |
| 60°-70°   | 0.3    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 771.2  | 86.3      |
| 0°-40°    | 879.6  | 98.4      |
| 0°-60°    | 893.6  | 100.0     |
| 0°-90°    | 894.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 894.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1182 |      |
| 5°  | 1136 | 110  |
| 15° | 1125 | 313  |
| 25° | 790  | 348  |
| 35° | 145  | 108  |
| 45° | 15   | 13   |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1297920

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3D1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1182.3 |
| 1°    | 1177.9 |
| 2°    | 1166.3 |
| 3°    | 1152.0 |
| 4°    | 1139.1 |
| 5°    | 1136.1 |
| 6°    | 1139.5 |
| 7°    | 1146.6 |
| 8°    | 1154.8 |
| 9°    | 1161.2 |
| 10°   | 1163.3 |
| 11°   | 1161.9 |
| 12°   | 1156.5 |
| 13°   | 1148.0 |
| 14°   | 1138.1 |
| 15°   | 1124.9 |
| 16°   | 1109.6 |
| 17°   | 1090.2 |
| 18°   | 1068.5 |
| 19°   | 1042.3 |
| 20°   | 1012.8 |
| 21°   | 979.2  |
| 22°   | 939.4  |
| 23°   | 895.6  |
| 24°   | 845.4  |
| 25°   | 790.0  |
| 26°   | 729.2  |
| 27°   | 664.7  |
| 28°   | 595.7  |
| 29°   | 524.7  |
| 30°   | 452.4  |
| 31°   | 379.7  |
| 32°   | 308.7  |
| 32.5° | 277.1  |
| 33°   | 244.5  |
| 34°   | 189.2  |
| 35°   | 145.0  |
| 36°   | 110.4  |
| 37°   | 81.9   |
| 37.5° | 70.0   |
| 38°   | 60.8   |
| 39°   | 46.2   |
| 40°   | 37.4   |
| 42.5° | 23.8   |
| 45°   | 15.3   |



TEST NUMBER: P1297920  
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3D1WMH\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 47.5° | 9.2 |
| 50°   | 4.1 |
| 52.5° | 1.4 |
| 55°   | 0.7 |
| 57.5° | 0.3 |
| 60°   | 0.3 |
| 62.5° | 0.3 |
| 65°   | 0.3 |
| 67.5° | 0.3 |
| 70°   | 0.3 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)