

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296009

Luminaire Tested: P3AS13R25W2N902750DE010 E3DL1H\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296009  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902750DE010 E3DL1H\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 808.0 lumens  
Efficiency: N/A  
Efficacy: 65.7 lumens/watt  
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296009  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1H\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1296009

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1H\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	194.9	24.1
10°-20°	318.4	39.4
20°-30°	182.0	22.5
30°-40°	71.8	8.9
40°-50°	22.0	2.7
50°-60°	8.7	1.1
60°-70°	5.8	0.7
70°-80°	3.3	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	695.3	86.1
0°-40°	767.1	94.9
0°-60°	797.9	98.7
0°-90°	808.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	808.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2364	
5°	2197	195
15°	1158	318
25°	384	182
35°	109	72
45°	26	22
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1296009

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1H\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2363.6
1°	2359.0
2°	2339.7
3°	2305.7
4°	2258.6
5°	2196.9
6°	2124.3
7°	2042.4
8°	1947.4
9°	1850.1
10°	1739.7
11°	1630.8
12°	1511.2
13°	1393.0
14°	1271.8
15°	1158.3
17.5°	898.0
20°	681.8
22.5°	512.0
25°	384.5
27.5°	284.9
30°	209.3
32.5°	151.3
35°	108.9
37.5°	77.2
40°	54.1
42.5°	37.1
45°	26.3
47.5°	18.5
50°	13.9
52.5°	10.8
55°	9.3
57.5°	8.5
60°	6.9
62.5°	6.2
65°	6.2
67.5°	5.4
70°	4.6
72.5°	3.9
75°	3.1
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.8



TEST NUMBER: P1296009  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1H\_5000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)