

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296026

Luminaire Tested: P3AS13R25W2N902750DE010 E3DL1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296026
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902750DE010 E3DL1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 800.0 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296026
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296026
 CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	86	81	78	84	80	77	83	79	77	82	78	76	75	75	75	75
7	90	83	78	74	89	82	77	74	81	77	74	80	76	73	79	75	73	72	72	72	72
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
9	84	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	67	66	66	66	66
10	81	73	69	65	80	73	68	65	72	68	65	72	68	65	71	67	65	64	64	64	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	513161
5°	478779
10°	383538
15°	260342
20°	157537
25°	92110
30°	52464
35°	28857
40°	15314
45°	8063
50°	4708
55°	3517
60°	3026
65°	3165
70°	2949
75°	2626
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8063 cd/sqm



TEST NUMBER: P1296026

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.0	24.1
10°-20°	315.3	39.4
20°-30°	180.2	22.5
30°-40°	71.1	8.9
40°-50°	21.8	2.7
50°-60°	8.6	1.1
60°-70°	5.8	0.7
70°-80°	3.2	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	688.5	86.1
0°-40°	759.6	94.9
0°-60°	790.0	98.7
0°-90°	800.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	800.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2340	
5°	2175	193
15°	1147	315
25°	381	180
35°	108	71
45°	26	22
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1296026
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2340.2
1°	2335.7
2°	2316.5
3°	2282.9
4°	2236.3
5°	2175.1
6°	2103.2
7°	2022.2
8°	1928.2
9°	1831.8
10°	1722.5
11°	1614.7
12°	1496.2
13°	1379.2
14°	1259.2
15°	1146.8
17.5°	889.2
20°	675.1
22.5°	506.9
25°	380.7
27.5°	282.1
30°	207.2
32.5°	149.8
35°	107.8
37.5°	76.5
40°	53.5
42.5°	36.7
45°	26.0
47.5°	18.3
50°	13.8
52.5°	10.7
55°	9.2
57.5°	8.4
60°	6.9
62.5°	6.1
65°	6.1
67.5°	5.4
70°	4.6
72.5°	3.8
75°	3.1
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.8



TEST NUMBER: P1296026
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)