

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297940

Luminaire Tested: P3AS13R55W2N902750DE010 E3DL1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297940
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55W2N902750DE010 E3DL1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 755.0 lumens
Efficiency: N/A
Efficacy: 61.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297940
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DL1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1297940

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DL1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | |
| 1 | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 | 101 | 99 | 98 | 97 | 96 | 95 | 93 | | | |
| 2 | 108 | 103 | 99 | 95 | 106 | 101 | 97 | 94 | 98 | 95 | 92 | 95 | 92 | 90 | 92 | 90 | 88 | 87 | | | |
| 3 | 102 | 96 | 91 | 87 | 100 | 94 | 90 | 86 | 92 | 88 | 85 | 89 | 86 | 83 | 87 | 85 | 82 | 81 | | | |
| 4 | 97 | 90 | 84 | 80 | 95 | 89 | 83 | 79 | 86 | 82 | 78 | 84 | 81 | 78 | 82 | 79 | 77 | 75 | | | |
| 5 | 92 | 84 | 78 | 74 | 91 | 83 | 78 | 74 | 81 | 77 | 73 | 80 | 76 | 72 | 78 | 75 | 72 | 70 | | | |
| 6 | 88 | 79 | 73 | 69 | 86 | 78 | 73 | 68 | 77 | 72 | 68 | 75 | 71 | 68 | 74 | 70 | 67 | 66 | | | |
| 7 | 84 | 74 | 68 | 64 | 82 | 74 | 68 | 64 | 72 | 67 | 64 | 71 | 67 | 63 | 70 | 66 | 63 | 62 | | | |
| 8 | 80 | 70 | 64 | 60 | 78 | 70 | 64 | 60 | 69 | 63 | 60 | 67 | 63 | 60 | 67 | 62 | 59 | 58 | | | |
| 9 | 76 | 66 | 61 | 57 | 75 | 66 | 60 | 56 | 65 | 60 | 56 | 64 | 59 | 56 | 63 | 59 | 56 | 55 | | | |
| 10 | 73 | 63 | 57 | 53 | 72 | 62 | 57 | 53 | 62 | 57 | 53 | 61 | 56 | 53 | 60 | 56 | 53 | 52 | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 207308 |
| 5° | 205216 |
| 10° | 198170 |
| 15° | 183179 |
| 20° | 158074 |
| 25° | 124846 |
| 30° | 88571 |
| 35° | 57099 |
| 40° | 34293 |
| 45° | 19320 |
| 50° | 10405 |
| 55° | 3708 |
| 60° | 3333 |
| 65° | 3217 |
| 70° | 3077 |
| 75° | 2965 |
| 80° | 2652 |
| 85° | 1761 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19320 cd/sqm



TEST NUMBER: P1297940

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DL1MW_2700K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 87.7 | 11.6 |
| 10°-20° | 223.1 | 29.6 |
| 20°-30° | 233.8 | 31.0 |
| 30°-40° | 136.4 | 18.1 |
| 40°-50° | 51.0 | 6.8 |
| 50°-60° | 12.0 | 1.6 |
| 60°-70° | 6.1 | 0.8 |
| 70°-80° | 3.7 | 0.5 |
| 80°-90° | 1.0 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 544.6 | 72.1 |
| 0°-40° | 681.1 | 90.2 |
| 0°-60° | 744.1 | 98.6 |
| 0°-90° | 755.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 755.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 945 | |
| 5° | 932 | 88 |
| 15° | 807 | 223 |
| 25° | 516 | 234 |
| 35° | 213 | 136 |
| 45° | 62 | 51 |
| 55° | 10 | 12 |
| 65° | 6 | 6 |
| 75° | 4 | 4 |
| 85° | 1 | 1 |
| 90° | 0 | |



TEST NUMBER: P1297940
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DL1MW_2700K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 945.4 |
| 2.5° | 942.7 |
| 5° | 932.3 |
| 7.5° | 915.7 |
| 10° | 890.0 |
| 12.5° | 854.0 |
| 15° | 806.9 |
| 17.5° | 747.4 |
| 20° | 677.4 |
| 22.5° | 599.1 |
| 25° | 516.0 |
| 27.5° | 430.8 |
| 30° | 349.8 |
| 32.5° | 276.4 |
| 35° | 213.3 |
| 37.5° | 162.1 |
| 40° | 119.8 |
| 42.5° | 85.9 |
| 45° | 62.3 |
| 47.5° | 45.0 |
| 50° | 30.5 |
| 52.5° | 17.3 |
| 55° | 9.7 |
| 57.5° | 8.3 |
| 60° | 7.6 |
| 62.5° | 6.9 |
| 65° | 6.2 |
| 67.5° | 5.5 |
| 70° | 4.8 |
| 72.5° | 4.2 |
| 75° | 3.5 |
| 77.5° | 2.8 |
| 80° | 2.1 |
| 82.5° | 1.4 |
| 85° | 0.7 |
| 87.5° | 0.7 |
| 90° | 0.0 |

(END OF REPORT)