

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298002

Luminaire Tested: P3AS13R55W2N902750DE010 E3DLP1MW\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298002  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R55W2N902750DE010 E3DLP1MW\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3500K CCT AND, 90CRI ,  
E3DLP1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 564.0 lumens  
Efficiency: N/A  
Efficacy: 45.9 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298002  
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1MW\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1298002  
 CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1MW\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92			
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	85			
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	85	83	80	79			
4	96	88	82	77	94	87	81	77	84	80	76	82	78	75	80	77	74	73			
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	67			
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63			
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59			
8	78	68	62	57	76	67	61	57	66	61	57	65	60	57	64	60	56	55			
9	74	64	58	54	73	63	58	54	62	57	53	62	57	53	61	56	53	52			
10	70	60	55	51	69	60	54	50	59	54	50	58	54	50	58	53	50	49			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	153431
5°	149570
10°	139053
15°	123837
20°	105242
25°	84924
30°	64744
35°	46043
40°	30400
45°	18017
50°	10575
55°	6499
60°	5789
65°	5241
70°	4488
75°	3897
80°	3915
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18017 cd/sqm



TEST NUMBER: P1298002

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1MW\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.1	11.2
10°-20°	151.2	26.8
20°-30°	160.2	28.4
30°-40°	108.2	19.2
40°-50°	47.4	8.4
50°-60°	17.0	3.0
60°-70°	10.0	1.8
70°-80°	5.2	0.9
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	374.5	66.4
0°-40°	482.7	85.6
0°-60°	547.1	97.0
0°-90°	564.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	564.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	700	
5°	680	63
15°	546	151
25°	351	160
35°	172	108
45°	58	47
55°	17	17
65°	10	10
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1298002  
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1MW\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	699.7
2.5°	694.3
5°	679.5
7.5°	655.5
10°	624.5
12.5°	587.3
15°	545.5
17.5°	499.0
20°	451.0
22.5°	400.6
25°	351.0
27.5°	302.2
30°	255.7
32.5°	211.5
35°	172.0
37.5°	136.4
40°	106.2
42.5°	79.8
45°	58.1
47.5°	42.6
50°	31.0
52.5°	21.7
55°	17.0
57.5°	15.5
60°	13.2
62.5°	11.6
65°	10.1
67.5°	8.5
70°	7.0
72.5°	6.2
75°	4.6
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)