

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296033

Luminaire Tested: P3AS13R25W2N902750DE010 E3DLD1GPH\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296033  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902750DE010 E3DLD1GPH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 305.0 lumens  
Efficiency: N/A  
Efficacy: 24.8 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296033  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1GPH\_4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296033

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1GPH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	72494
5°	70768
10°	65574
15°	58389
20°	50194
25°	42656
30°	35119
35°	27358
40°	19694
45°	12497
50°	7403
55°	5085
60°	4649
65°	4358
70°	3911
75°	3558
80°	3410
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 12497 cd/sqm



TEST NUMBER: P1296033

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1GPH\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	29.8	9.8
10°-20°	71.4	23.4
20°-30°	80.7	26.5
30°-40°	63.8	20.9
40°-50°	32.3	10.6
50°-60°	12.9	4.2
60°-70°	8.3	2.7
70°-80°	4.6	1.5
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.9	59.6
0°-40°	245.7	80.6
0°-60°	290.9	95.4
0°-90°	305.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	305.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	331	
5°	322	30
15°	257	71
25°	176	81
35°	102	64
45°	40	32
55°	13	13
65°	8	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1296033  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1GPH\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	330.6
1°	330.6
2°	329.4
3°	327.5
4°	324.9
5°	321.5
6°	317.3
7°	312.3
8°	307.0
9°	300.9
10°	294.5
11°	287.3
12°	280.4
13°	272.4
14°	264.8
15°	257.2
17.5°	236.0
20°	215.1
22.5°	195.3
25°	176.3
27.5°	157.7
30°	138.7
32.5°	120.8
35°	102.2
37.5°	85.1
40°	68.8
42.5°	53.6
45°	40.3
47.5°	30.0
50°	21.7
52.5°	16.3
55°	13.3
57.5°	12.2
60°	10.6
62.5°	9.5
65°	8.4
67.5°	7.2
70°	6.1
72.5°	5.3
75°	4.2
77.5°	3.4
80°	2.7
82.5°	1.9
85°	1.1
87.5°	0.4



TEST NUMBER: P1296033  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1GPH\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)