

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296036

Luminaire Tested: P3AS13R25W2N902750DE010 E3DLD1H\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296036  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902750DE010 E3DLD1H\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,  
E3DLD1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 614.0 lumens  
Efficiency: N/A  
Efficacy: 49.9 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296036  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1H\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296036

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1H\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	145931
5°	142439
10°	131995
15°	117549
20°	101019
25°	85868
30°	70694
35°	55091
40°	39617
45°	25150
50°	14874
55°	10246
60°	9385
65°	8717
70°	7822
75°	7117
80°	6819
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 25150 cd/sqm



TEST NUMBER: P1296036

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1H\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.0	9.8
10°-20°	143.8	23.4
20°-30°	162.4	26.5
30°-40°	128.5	20.9
40°-50°	64.9	10.6
50°-60°	26.0	4.2
60°-70°	16.6	2.7
70°-80°	9.2	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.2	59.6
0°-40°	494.7	80.6
0°-60°	585.6	95.4
0°-90°	614.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	614.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	666	
5°	647	60
15°	518	144
25°	355	162
35°	206	128
45°	81	65
55°	27	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296036  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1H\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	665.5
1°	665.5
2°	663.2
3°	659.4
4°	654.0
5°	647.1
6°	638.7
7°	628.8
8°	618.1
9°	605.8
10°	592.8
11°	578.3
12°	564.5
13°	548.4
14°	533.1
15°	517.8
17.5°	475.0
20°	432.9
22.5°	393.2
25°	354.9
27.5°	317.4
30°	279.2
32.5°	243.2
35°	205.8
37.5°	171.3
40°	138.4
42.5°	107.9
45°	81.1
47.5°	60.4
50°	43.6
52.5°	32.9
55°	26.8
57.5°	24.5
60°	21.4
62.5°	19.1
65°	16.8
67.5°	14.5
70°	12.2
72.5°	10.7
75°	8.4
77.5°	6.9
80°	5.4
82.5°	3.8
85°	2.3
87.5°	0.8



TEST NUMBER: P1296036  
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLD1H\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)