

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298037

Luminaire Tested: P3AS13R55W2N902765DE010 E3CD1MB\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298037  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R55W2N902765DE010 E3CD1MB\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,  
E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1026.9 lumens  
Efficiency: N/A  
Efficacy: 83.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298037  
CATALOG NUMBER: P3AS13R55W2N902765DE010 E3CD1MB\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1298037

CATALOG NUMBER: P3AS13R55W2N902765DE010 E3CD1MB\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	123.9	12.1
10°-20°	354.4	34.5
20°-30°	395.1	38.5
30°-40°	129.2	12.6
40°-50°	17.0	1.7
50°-60°	3.6	0.4
60°-70°	2.1	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	873.4	85.0
0°-40°	1002.6	97.6
0°-60°	1023.2	99.6
0°-90°	1026.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1026.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1299	
5°	1282	124
15°	1275	354
25°	898	395
35°	171	129
45°	20	17
55°	3	4
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1298037  
CATALOG NUMBER: P3AS13R55W2N902765DE010 E3CD1MB\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1299.0
2.5°	1289.7
5°	1282.0
7.5°	1300.5
10°	1318.3
12.5°	1309.0
15°	1275.1
17.5°	1221.0
20°	1143.9
22.5°	1037.3
25°	897.6
27.5°	720.1
30°	521.0
32.5°	319.5
35°	170.6
37.5°	86.4
40°	45.5
42.5°	29.3
45°	20.1
47.5°	13.9
50°	7.7
52.5°	4.6
55°	3.1
57.5°	3.1
60°	3.1
62.5°	2.3
65°	2.3
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)