

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298052

Luminaire Tested: P3AS13R55W2N902765DE010 E3D1H\_3000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1298052  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R55W2N902765DE010 E3D1H\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 986.0 lumens  
Efficiency: N/A  
Efficacy: 80.2 lumens/watt  
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298052

CATALOG NUMBER: P3AS13R55W2N902765DE010 E3D1H\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1298052

CATALOG NUMBER: P3AS13R55W2N902765DE010 E3D1H\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.2	12.3
10°-20°	345.4	35.0
20°-30°	383.9	38.9
30°-40°	119.5	12.1
40°-50°	14.4	1.5
50°-60°	1.1	0.1
60°-70°	0.4	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	850.6	86.3
0°-40°	970.1	98.4
0°-60°	985.6	100.0
0°-90°	986.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	986.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1304	
5°	1253	121
15°	1241	345
25°	871	384
35°	160	120
45°	17	14
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1298052

CATALOG NUMBER: P3AS13R55W2N902765DE010 E3D1H\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1303.9
1°	1299.1
2°	1286.3
3°	1270.6
4°	1256.4
5°	1253.0
6°	1256.7
7°	1264.6
8°	1273.6
9°	1280.7
10°	1283.0
11°	1281.5
12°	1275.5
13°	1266.1
14°	1255.2
15°	1240.6
16°	1223.8
17°	1202.4
18°	1178.5
19°	1149.6
20°	1117.0
21°	1079.9
22°	1036.1
23°	987.8
24°	932.3
25°	871.3
26°	804.2
27°	733.1
28°	657.0
29°	578.7
30°	499.0
31°	418.8
32°	340.5
32.5°	305.7
33°	269.7
34°	208.6
35°	159.9
36°	121.7
37°	90.3
37.5°	77.2
38°	67.1
39°	50.9
40°	41.2
42.5°	26.2
45°	16.9



TEST NUMBER: P1298052

CATALOG NUMBER: P3AS13R55W2N902765DE010 E3D1H\_3000K

**CANDELA DISTRIBUTION (continued):**

	0°
47.5°	10.1
50°	4.5
52.5°	1.5
55°	0.7
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)