

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296075

Luminaire Tested: P3AS13R25W2N902750DE010 E3DLP1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296075
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902750DE010 E3DLP1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 444.0 lumens
Efficiency: N/A
Efficacy: 36.1 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296075
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLP1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1296075
 CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLP1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	161193
5°	154655
10°	135468
15°	108900
20°	83681
25°	63318
30°	45754
35°	30383
40°	18435
45°	10730
50°	6857
55°	5543
60°	4868
65°	4307
70°	3526
75°	3558
80°	2652
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10730 cd/sqm



TEST NUMBER: P1296075

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLP1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.0	14.4
10°-20°	132.6	29.9
20°-30°	120.0	27.0
30°-40°	72.1	16.2
40°-50°	28.6	6.4
50°-60°	13.2	3.0
60°-70°	8.0	1.8
70°-80°	4.3	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	316.6	71.3
0°-40°	388.6	87.5
0°-60°	430.5	96.9
0°-90°	444.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	444.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	735	
5°	703	64
15°	480	133
25°	262	120
35°	114	72
45°	35	29
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1296075
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLP1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	735.1
1°	735.1
2°	731.7
3°	724.0
4°	714.3
5°	702.6
6°	687.4
7°	670.0
8°	650.0
9°	629.9
10°	608.4
11°	583.5
12°	557.9
13°	532.3
14°	506.7
15°	479.7
17.5°	416.0
20°	358.6
22.5°	306.6
25°	261.7
27.5°	219.4
30°	180.7
32.5°	145.4
35°	113.5
37.5°	86.5
40°	64.4
42.5°	47.1
45°	34.6
47.5°	26.3
50°	20.1
52.5°	16.6
55°	14.5
57.5°	12.5
60°	11.1
62.5°	9.0
65°	8.3
67.5°	6.9
70°	5.5
72.5°	4.8
75°	4.2
77.5°	3.5
80°	2.1
82.5°	1.4
85°	1.4
87.5°	0.7



TEST NUMBER: P1296075
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLP1MW_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)