

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298086

Luminaire Tested: P3AS13R55W2N902765DE010 E3DL1GPH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298086  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R55W2N902765DE010 E3DL1GPH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 6500K CCT AND, 90CRI ,  
E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 412.0 lumens  
Efficiency: N/A  
Efficacy: 33.5 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298086  
CATALOG NUMBER: P3AS13R55W2N902765DE010 E3DL1GPH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1298086

CATALOG NUMBER: P3AS13R55W2N902765DE010 E3DL1GPH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93				93
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87				87
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81				81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75				75
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66				66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62				62
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58				58
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55				55
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52				52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	113127
5°	111974
10°	108148
15°	99955
20°	86271
25°	68133
30°	48337
35°	31159
40°	18721
45°	10544
50°	5663
55°	2026
60°	1842
65°	1764
70°	1667
75°	1610
80°	1389
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10544 cd/sqm



TEST NUMBER: P1298086

CATALOG NUMBER: P3AS13R55W2N902765DE010 E3DL1GPH\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	47.8	11.6
10°-20°	121.8	29.6
20°-30°	127.6	31.0
30°-40°	74.4	18.1
40°-50°	27.9	6.8
50°-60°	6.5	1.6
60°-70°	3.4	0.8
70°-80°	2.0	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	297.2	72.1
0°-40°	371.7	90.2
0°-60°	406.1	98.6
0°-90°	412.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	412.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	516	
5°	509	48
15°	440	122
25°	282	128
35°	116	74
45°	34	28
55°	5	7
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1298086  
CATALOG NUMBER: P3AS13R55W2N902765DE010 E3DL1GPH\_6500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	515.9
2.5°	514.4
5°	508.7
7.5°	499.7
10°	485.7
12.5°	466.0
15°	440.3
17.5°	407.8
20°	369.7
22.5°	326.9
25°	281.6
27.5°	235.1
30°	190.9
32.5°	150.8
35°	116.4
37.5°	88.4
40°	65.4
42.5°	46.9
45°	34.0
47.5°	24.6
50°	16.6
52.5°	9.4
55°	5.3
57.5°	4.5
60°	4.2
62.5°	3.8
65°	3.4
67.5°	3.0
70°	2.6
72.5°	2.3
75°	1.9
77.5°	1.5
80°	1.1
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)