

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296076

Luminaire Tested: P3AS13R25W2N902750DE010 E3DLP1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902750DE010 E3DLP1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 3000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 490.0 lumens
Efficiency: N/A
Efficacy: 39.8 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296076
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLP1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296076

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLP1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177902
5°	170680
10°	149518
15°	120182
20°	92338
25°	69875
30°	50489
35°	33542
40°	20324
45°	11846
50°	7573
55°	6117
60°	5350
65°	4774
70°	3911
75°	3897
80°	2904
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11846 cd/sqm



TEST NUMBER: P1296076

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.6	14.4
10°-20°	146.4	29.9
20°-30°	132.4	27.0
30°-40°	79.5	16.2
40°-50°	31.6	6.4
50°-60°	14.6	3.0
60°-70°	8.9	1.8
70°-80°	4.7	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.4	71.3
0°-40°	428.9	87.5
0°-60°	475.0	97.0
0°-90°	490.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	490.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	811	
5°	775	71
15°	529	146
25°	289	132
35°	125	80
45°	38	32
55°	16	15
65°	9	9
75°	5	5
85°	2	1
90°	0	



TEST NUMBER: P1296076
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	811.3
1°	811.3
2°	807.5
3°	799.1
4°	788.4
5°	775.4
6°	758.6
7°	739.5
8°	717.3
9°	695.2
10°	671.5
11°	644.0
12°	615.7
13°	587.4
14°	559.2
15°	529.4
17.5°	459.1
20°	395.7
22.5°	338.4
25°	288.8
27.5°	242.2
30°	199.4
32.5°	160.4
35°	125.3
37.5°	95.5
40°	71.0
42.5°	51.9
45°	38.2
47.5°	29.0
50°	22.2
52.5°	18.3
55°	16.0
57.5°	13.8
60°	12.2
62.5°	9.9
65°	9.2
67.5°	7.6
70°	6.1
72.5°	5.3
75°	4.6
77.5°	3.8
80°	2.3
82.5°	1.5
85°	1.5
87.5°	0.8



TEST NUMBER: P1296076
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3DLP1MW_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)