

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296095

Luminaire Tested: P3AS13R25W2N902750DE010 E3PHLD1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296095
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902750DE010 E3PHLD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 556.0 lumens
Efficiency: N/A
Efficacy: 45.2 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296095
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3PHLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1296095

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3PHLD1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86	90	87	84	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	83	78	75	80	77	74	72
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	86	76	68	63	84	75	68	63	73	67	62	71	66	62	69	65	61	59
6	81	70	63	58	79	69	62	57	68	62	57	66	61	57	65	60	56	55
7	76	65	58	53	75	64	58	53	63	57	53	62	56	52	61	56	52	50
8	72	61	54	49	71	60	54	49	59	53	49	58	53	49	57	52	48	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	43	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145076
5°	137706
10°	119281
15°	97095
20°	76727
25°	61165
30°	49603
35°	40395
40°	33463
45°	28189
50°	23880
55°	21027
60°	18420
65°	16085
70°	14105
75°	11861
80°	8840
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 28189 cd/sqm



TEST NUMBER: P1296095

CATALOG NUMBER: P3AS13R25W2N902750DE010 E3PHLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.8	10.2
10°-20°	118.6	21.3
20°-30°	116.9	21.0
30°-40°	95.2	17.1
40°-50°	70.6	12.7
50°-60°	49.3	8.9
60°-70°	30.9	5.6
70°-80°	14.9	2.7
80°-90°	2.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	292.3	52.6
0°-40°	387.5	69.7
0°-60°	507.4	91.3
0°-90°	556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	662	
5°	626	57
15°	428	119
25°	253	117
35°	151	95
45°	91	71
55°	55	49
65°	31	31
75°	14	15
85°	2	3
90°	0	



TEST NUMBER: P1296095
CATALOG NUMBER: P3AS13R25W2N902750DE010 E3PHLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	661.6
2.5°	652.6
5°	625.6
7.5°	584.6
10°	535.7
12.5°	481.7
15°	427.7
17.5°	374.8
20°	328.8
22.5°	288.8
25°	252.8
27.5°	221.9
30°	195.9
32.5°	171.9
35°	150.9
37.5°	132.9
40°	116.9
42.5°	102.9
45°	90.9
47.5°	79.9
50°	70.0
52.5°	62.0
55°	55.0
57.5°	48.0
60°	42.0
62.5°	36.0
65°	31.0
67.5°	26.0
70°	22.0
72.5°	18.0
75°	14.0
77.5°	10.0
80°	7.0
82.5°	4.0
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)