

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296180

Luminaire Tested: P3AS13R25W2N902765DE010 E3DL1H\_4000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296180  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902765DE010 E3DL1H\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 812.0 lumens  
Efficiency: N/A  
Efficacy: 66.0 lumens/watt  
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296180  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DL1H\_4000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1296180

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DL1H\_4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	195.9	24.1
10°-20°	320.0	39.4
20°-30°	182.9	22.5
30°-40°	72.2	8.9
40°-50°	22.1	2.7
50°-60°	8.7	1.1
60°-70°	5.9	0.7
70°-80°	3.3	0.4
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	698.8	86.1
0°-40°	770.9	94.9
0°-60°	801.8	98.7
0°-90°	812.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	812.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2375	
5°	2208	196
15°	1164	320
25°	386	183
35°	109	72
45°	26	22
55°	9	9
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1296180  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DL1H\_4000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2375.3
1°	2370.7
2°	2351.3
3°	2317.1
4°	2269.8
5°	2207.7
6°	2134.8
7°	2052.5
8°	1957.1
9°	1859.3
10°	1748.3
11°	1638.9
12°	1518.6
13°	1399.9
14°	1278.1
15°	1164.0
17.5°	902.5
20°	685.2
22.5°	514.5
25°	386.4
27.5°	286.3
30°	210.3
32.5°	152.1
35°	109.4
37.5°	77.6
40°	54.3
42.5°	37.2
45°	26.4
47.5°	18.6
50°	14.0
52.5°	10.9
55°	9.3
57.5°	8.5
60°	7.0
62.5°	6.2
65°	6.2
67.5°	5.4
70°	4.7
72.5°	3.9
75°	3.1
77.5°	2.3
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.8



TEST NUMBER: P1296180  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DL1H\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)