

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296207

Luminaire Tested: P3AS13R25W2N902765DE010 E3DLD1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296207  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902765DE010 E3DLD1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 273.0 lumens  
Efficiency: N/A  
Efficacy: 22.2 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296207  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLD1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296207

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLD1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	64885
5°	63328
10°	58694
15°	52259
20°	44921
25°	38180
30°	31423
35°	24494
40°	17633
45°	11195
50°	6618
55°	4549
60°	4166
65°	3891
70°	3462
75°	3135
80°	3031
85°	2516

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 11195 cd/sqm



TEST NUMBER: P1296207

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLD1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.7	9.8
10°-20°	63.9	23.4
20°-30°	72.2	26.4
30°-40°	57.1	20.9
40°-50°	28.9	10.6
50°-60°	11.6	4.2
60°-70°	7.4	2.7
70°-80°	4.1	1.5
80°-90°	1.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	162.8	59.6
0°-40°	220.0	80.6
0°-60°	260.4	95.4
0°-90°	273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	273.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	296	
5°	288	27
15°	230	64
25°	158	72
35°	92	57
45°	36	29
55°	12	12
65°	8	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1296207  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLD1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	295.9
1°	295.9
2°	294.9
3°	293.2
4°	290.8
5°	287.7
6°	284.0
7°	279.6
8°	274.8
9°	269.4
10°	263.6
11°	257.1
12°	251.0
13°	243.9
14°	237.1
15°	230.2
17.5°	211.2
20°	192.5
22.5°	174.8
25°	157.8
27.5°	141.1
30°	124.1
32.5°	108.2
35°	91.5
37.5°	76.2
40°	61.6
42.5°	48.0
45°	36.1
47.5°	26.9
50°	19.4
52.5°	14.6
55°	11.9
57.5°	10.9
60°	9.5
62.5°	8.5
65°	7.5
67.5°	6.5
70°	5.4
72.5°	4.8
75°	3.7
77.5°	3.1
80°	2.4
82.5°	1.7
85°	1.0
87.5°	0.3



TEST NUMBER: P1296207  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLD1GPH\_2700K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)