

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298245

Luminaire Tested: P3AS13R60W2N902750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298245
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R60W2N902750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 394.0 lumens
Efficiency: N/A
Efficacy: 32.0 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298245
CATALOG NUMBER: P3AS13R60W2N902750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298245
 CATALOG NUMBER: P3AS13R60W2N902750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68	68	68	68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63	63	63	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59	59	59	59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55	55	55	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48	48	48	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	93041
5°	92164
10°	89466
15°	83814
20°	74183
25°	62060
30°	48640
35°	35282
40°	23473
45°	14637
50°	7914
55°	2294
60°	2149
65°	1920
70°	1923
75°	1864
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14637 cd/sqm



TEST NUMBER: P1298245

CATALOG NUMBER: P3AS13R60W2N902750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.4	10.0
10°-20°	102.4	26.0
20°-30°	116.8	29.6
30°-40°	82.8	21.0
40°-50°	37.6	9.5
50°-60°	8.0	2.0
60°-70°	3.8	1.0
70°-80°	2.4	0.6
80°-90°	0.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	258.6	65.6
0°-40°	341.4	86.7
0°-60°	387.0	98.2
0°-90°	394.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	394.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	424	
5°	419	39
15°	369	102
25°	256	117
35°	132	83
45°	47	38
55°	6	8
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1298245
CATALOG NUMBER: P3AS13R60W2N902750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	424.3
2.5°	422.8
5°	418.7
7.5°	411.5
10°	401.8
12.5°	388.0
15°	369.2
17.5°	345.6
20°	317.9
22.5°	288.0
25°	256.5
27.5°	224.3
30°	192.1
32.5°	161.4
35°	131.8
37.5°	105.6
40°	82.0
42.5°	62.2
45°	47.2
47.5°	35.2
50°	23.2
52.5°	10.9
55°	6.0
57.5°	5.2
60°	4.9
62.5°	4.5
65°	3.7
67.5°	3.4
70°	3.0
72.5°	2.6
75°	2.2
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)