

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296241

Luminaire Tested: P3AS13R25W2N902765DE010 E3DLD1WMH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296241  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R25W2N902765DE010 E3DLD1WMH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 5000K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 619.0 lumens  
Efficiency: N/A  
Efficacy: 50.3 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296241  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLD1WMH\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1296241

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLD1WMH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.5	9.8
10°-20°	144.9	23.4
20°-30°	163.8	26.5
30°-40°	129.5	20.9
40°-50°	65.4	10.6
50°-60°	26.2	4.2
60°-70°	16.8	2.7
70°-80°	9.2	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.2	59.6
0°-40°	498.7	80.6
0°-60°	590.4	95.4
0°-90°	619.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	619.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	671	
5°	652	61
15°	522	145
25°	358	164
35°	207	130
45°	82	65
55°	27	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296241  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLD1WMH\_5000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	670.9
1°	670.9
2°	668.6
3°	664.7
4°	659.3
5°	652.4
6°	643.9
7°	633.9
8°	623.1
9°	610.7
10°	597.6
11°	583.0
12°	569.1
13°	552.9
14°	537.5
15°	522.1
17.5°	478.9
20°	436.5
22.5°	396.4
25°	357.8
27.5°	320.0
30°	281.5
32.5°	245.2
35°	207.4
37.5°	172.7
40°	139.6
42.5°	108.7
45°	81.7
47.5°	60.9
50°	44.0
52.5°	33.2
55°	27.0
57.5°	24.7
60°	21.6
62.5°	19.3
65°	17.0
67.5°	14.7
70°	12.3
72.5°	10.8
75°	8.5
77.5°	6.9
80°	5.4
82.5°	3.9
85°	2.3
87.5°	0.8



TEST NUMBER: P1296241  
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLD1WMH\_5000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)