

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296243

Luminaire Tested: P3AS13R25W2N902765DE010 E3DLP1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902765DE010 E3DLP1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 2700K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 218.0 lumens
Efficiency: N/A
Efficacy: 17.7 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296243
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLP1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1296243

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLP1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	93
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	92	90	86
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	87	84	82
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	84	80	75
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	82	79	76
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	78	74	71
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	74	70	67
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	70	66	63
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	67	63	60
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	64	59	56
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	61	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79138
5°	75941
10°	66510
15°	53462
20°	41070
25°	31091
30°	22459
35°	14910
40°	9046
45°	5272
50°	3377
55°	2714
60°	2368
65°	2127
70°	1731
75°	1694
80°	1263
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5272 cd/sqm



TEST NUMBER: P1296243

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLP1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	31.4	14.4
10°-20°	65.1	29.9
20°-30°	58.9	27.0
30°-40°	35.4	16.2
40°-50°	14.1	6.4
50°-60°	6.5	3.0
60°-70°	3.9	1.8
70°-80°	2.1	1.0
80°-90°	0.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	155.4	71.3
0°-40°	190.8	87.5
0°-60°	211.3	97.0
0°-90°	218.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	218.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	361	
5°	345	31
15°	236	65
25°	128	59
35°	56	35
45°	17	14
55°	7	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1296243
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	360.9
1°	360.9
2°	359.2
3°	355.5
4°	350.7
5°	345.0
6°	337.5
7°	329.0
8°	319.1
9°	309.3
10°	298.7
11°	286.5
12°	273.9
13°	261.4
14°	248.8
15°	235.5
17.5°	204.3
20°	176.0
22.5°	150.6
25°	128.5
27.5°	107.7
30°	88.7
32.5°	71.4
35°	55.7
37.5°	42.5
40°	31.6
42.5°	23.1
45°	17.0
47.5°	12.9
50°	9.9
52.5°	8.2
55°	7.1
57.5°	6.1
60°	5.4
62.5°	4.4
65°	4.1
67.5°	3.4
70°	2.7
72.5°	2.4
75°	2.0
77.5°	1.7
80°	1.0
82.5°	0.7
85°	0.7
87.5°	0.3



TEST NUMBER: P1296243
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLP1GPH_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)