

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296248

Luminaire Tested: P3AS13R25W2N902765DE010 E3DLP1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R25W2N902765DE010 E3DLP1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 6500K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 242.0 lumens
Efficiency: N/A
Efficacy: 19.7 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296248
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLP1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1296248

CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLP1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.9	14.4
10°-20°	72.3	29.9
20°-30°	65.4	27.0
30°-40°	39.3	16.2
40°-50°	15.6	6.4
50°-60°	7.2	3.0
60°-70°	4.4	1.8
70°-80°	2.3	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	172.5	71.3
0°-40°	211.8	87.5
0°-60°	234.6	96.9
0°-90°	242.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	242.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	401	
5°	383	35
15°	262	72
25°	143	65
35°	62	39
45°	19	16
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1296248
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLP1GPH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	400.7
1°	400.7
2°	398.8
3°	394.6
4°	389.4
5°	382.9
6°	374.6
7°	365.2
8°	354.3
9°	343.3
10°	331.6
11°	318.0
12°	304.1
13°	290.1
14°	276.2
15°	261.5
17.5°	226.7
20°	195.4
22.5°	167.1
25°	142.6
27.5°	119.6
30°	98.5
32.5°	79.2
35°	61.9
37.5°	47.2
40°	35.1
42.5°	25.7
45°	18.9
47.5°	14.3
50°	10.9
52.5°	9.1
55°	7.9
57.5°	6.8
60°	6.0
62.5°	4.9
65°	4.5
67.5°	3.8
70°	3.0
72.5°	2.6
75°	2.3
77.5°	1.9
80°	1.1
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1296248
CATALOG NUMBER: P3AS13R25W2N902765DE010 E3DLP1GPH_6500K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)