

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296336

Luminaire Tested: P3AS13R30W2N902750DE010 E3D1LI\_5000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296336  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R30W2N902750DE010 E3D1LI\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,  
E3D1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 974.0 lumens  
Efficiency: N/A  
Efficacy: 79.2 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296336  
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3D1LI\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296336

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3D1LI\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    | 0  |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 99 | 98 | 100 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 96 | 95 | 94  |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99  | 100 | 98  | 97  | 97  | 96  | 95  | 94  | 93 | 92 | 90  |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 97  | 95  | 97  | 95  | 93  | 95  | 93  | 92  | 90  | 89 | 88 | 88  |
| 4   | 105 | 99  | 95  | 92  | 103 | 98  | 95  | 92  | 96  | 93  | 91  | 94  | 92  | 90  | 93  | 91  | 89  | 88  | 86 | 85 | 85  |
| 5   | 101 | 96  | 92  | 89  | 100 | 95  | 91  | 88  | 93  | 90  | 87  | 92  | 89  | 87  | 90  | 88  | 86  | 85  | 84 | 83 | 82  |
| 6   | 99  | 92  | 88  | 85  | 97  | 92  | 88  | 85  | 90  | 87  | 84  | 89  | 86  | 84  | 88  | 85  | 83  | 82  | 81 | 80 | 80  |
| 7   | 96  | 89  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 82  | 87  | 84  | 81  | 86  | 83  | 81  | 80  | 79 | 78 | 78  |
| 8   | 93  | 87  | 83  | 80  | 92  | 86  | 82  | 80  | 85  | 82  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 78  | 77 | 76 | 76  |
| 9   | 91  | 84  | 80  | 77  | 90  | 84  | 80  | 77  | 83  | 79  | 77  | 82  | 79  | 77  | 82  | 79  | 77  | 76  | 75 | 74 | 74  |
| 10  | 88  | 82  | 78  | 75  | 88  | 81  | 78  | 75  | 81  | 77  | 75  | 80  | 77  | 75  | 80  | 77  | 75  | 74  | 73 | 72 | 72  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 774938 |
| 5°  | 764845 |
| 10° | 667768 |
| 15° | 424452 |
| 20° | 168155 |
| 25° | 56156  |
| 30° | 26131  |
| 35° | 11832  |
| 40° | 4551   |
| 45° | 2233   |
| 50° | 648    |
| 55° | 306    |
| 60° | 175    |
| 65° | 208    |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2233 cd/sqm



TEST NUMBER: P1296336

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3D1LI\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 317.7  | 32.6      |
| 10°-20°   | 492.6  | 50.6      |
| 20°-30°   | 127.0  | 13.0      |
| 30°-40°   | 29.8   | 3.1       |
| 40°-50°   | 5.8    | 0.6       |
| 50°-60°   | 0.7    | 0.1       |
| 60°-70°   | 0.3    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 937.3  | 96.2      |
| 0°-40°    | 967.2  | 99.3      |
| 0°-60°    | 973.7  | 100.0     |
| 0°-90°    | 974.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 974.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3534 |      |
| 5°  | 3475 | 318  |
| 15° | 1870 | 493  |
| 25° | 232  | 127  |
| 35° | 44   | 30   |
| 45° | 7    | 6    |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1296336

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3D1LI\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3534.0 |
| 1°    | 3531.4 |
| 2°    | 3523.1 |
| 3°    | 3513.6 |
| 4°    | 3499.6 |
| 5°    | 3474.7 |
| 6°    | 3434.2 |
| 7°    | 3366.9 |
| 8°    | 3275.0 |
| 9°    | 3155.2 |
| 10°   | 2999.0 |
| 11°   | 2813.4 |
| 12°   | 2610.7 |
| 13°   | 2377.4 |
| 14°   | 2133.2 |
| 15°   | 1869.7 |
| 16°   | 1611.4 |
| 17°   | 1362.6 |
| 18°   | 1124.1 |
| 19°   | 905.2  |
| 20°   | 720.6  |
| 21°   | 567.1  |
| 22°   | 446.1  |
| 23°   | 353.1  |
| 24°   | 282.8  |
| 25°   | 232.1  |
| 26°   | 193.6  |
| 27°   | 164.5  |
| 28°   | 142.2  |
| 29°   | 121.7  |
| 30°   | 103.2  |
| 32.5° | 65.0   |
| 35°   | 44.2   |
| 37.5° | 27.6   |
| 40°   | 15.9   |
| 42.5° | 10.6   |
| 45°   | 7.2    |
| 47.5° | 4.2    |
| 50°   | 1.9    |
| 52.5° | 0.8    |
| 55°   | 0.8    |
| 57.5° | 0.4    |
| 60°   | 0.4    |
| 62.5° | 0.4    |
| 65°   | 0.4    |



TEST NUMBER: P1296336  
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3D1LI\_5000K

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 67.5° | 0.4 |
| 70°   | 0.0 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)