

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298400

Luminaire Tested: P3AS13R60W2N902765DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298400
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R60W2N902765DE010 E3DL1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 357.0 lumens
Efficiency: N/A
Efficacy: 29.0 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298400
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1298400

CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.7	10.0
10°-20°	92.8	26.0
20°-30°	105.8	29.6
30°-40°	75.0	21.0
40°-50°	34.0	9.5
50°-60°	7.2	2.0
60°-70°	3.5	1.0
70°-80°	2.2	0.6
80°-90°	0.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	234.3	65.6
0°-40°	309.4	86.7
0°-60°	350.6	98.2
0°-90°	357.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	357.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	384	
5°	379	36
15°	335	93
25°	232	106
35°	119	75
45°	43	34
55°	5	7
65°	3	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1298400
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	384.4
2.5°	383.1
5°	379.3
7.5°	372.9
10°	364.1
12.5°	351.5
15°	334.6
17.5°	313.2
20°	288.1
22.5°	260.9
25°	232.4
27.5°	203.2
30°	174.1
32.5°	146.2
35°	119.4
37.5°	95.7
40°	74.3
42.5°	56.3
45°	42.8
47.5°	31.9
50°	21.0
52.5°	9.8
55°	5.4
57.5°	4.8
60°	4.4
62.5°	4.1
65°	3.4
67.5°	3.1
70°	2.7
72.5°	2.4
75°	2.0
77.5°	1.7
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)