

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296353

Luminaire Tested: P3AS13R30W2N902750DE010 E3DL1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296353
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30W2N902750DE010 E3DL1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 397.1 lumens
Efficiency: N/A
Efficacy: 32.3 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296353
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DL1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296353

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DL1GPH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	86	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	75	75	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	71	71	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	69	69	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	63	63	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	231670
5°	220492
10°	185456
15°	133758
20°	82957
25°	47180
30°	26207
35°	14268
40°	7528
45°	4062
50°	2183
55°	1453
60°	1316
65°	1349
70°	1218
75°	932
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4062 cd/sqm



TEST NUMBER: P1296353
 CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DL1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.2	22.7
10°-20°	160.3	40.4
20°-30°	92.7	23.3
30°-40°	35.2	8.9
40°-50°	10.8	2.7
50°-60°	3.7	0.9
60°-70°	2.5	0.6
70°-80°	1.3	0.3
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	343.2	86.4
0°-40°	378.4	95.3
0°-60°	392.8	98.9
0°-90°	397.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	397.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1056	
5°	1002	90
15°	589	160
25°	195	93
35°	53	35
45°	13	11
55°	4	4
65°	3	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1296353
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1056.5
1°	1055.7
2°	1049.3
3°	1037.3
4°	1022.3
5°	1001.7
6°	975.5
7°	946.2
8°	913.6
9°	874.6
10°	832.9
11°	787.9
12°	740.3
13°	690.4
14°	639.8
15°	589.2
17.5°	464.7
20°	355.5
22.5°	263.6
25°	195.0
27.5°	141.8
30°	103.5
32.5°	74.6
35°	53.3
37.5°	37.1
40°	26.3
42.5°	18.4
45°	13.1
47.5°	9.0
50°	6.4
52.5°	4.5
55°	3.8
57.5°	3.4
60°	3.0
62.5°	2.6
65°	2.6
67.5°	2.3
70°	1.9
72.5°	1.5
75°	1.1
77.5°	1.1
80°	0.8
82.5°	0.8
85°	0.4
87.5°	0.0



TEST NUMBER: P1296353
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DL1GPH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)