

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298437

Luminaire Tested: P3AS13R60W2N902765DE010 E3DLD1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298437  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R60W2N902765DE010 E3DLD1GPH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 309.0 lumens  
Efficiency: N/A  
Efficacy: 25.1 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298437  
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DLD1GPH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1298437

CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DLD1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	54842
5°	54237
10°	52348
15°	49467
20°	45597
25°	41277
30°	36664
35°	31320
40°	24904
45°	17552
50°	10507
55°	5314
60°	5087
65°	4670
70°	4360
75°	4151
80°	3788
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 17552 cd/sqm



TEST NUMBER: P1298437

CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DLD1GPH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.2	7.5
10°-20°	60.9	19.7
20°-30°	78.2	25.3
30°-40°	72.5	23.5
40°-50°	44.1	14.3
50°-60°	14.7	4.8
60°-70°	9.0	2.9
70°-80°	5.1	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	162.2	52.5
0°-40°	234.7	76.0
0°-60°	293.6	95.0
0°-90°	309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	309.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	250	
5°	246	23
15°	218	61
25°	171	78
35°	117	72
45°	57	44
55°	14	15
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1298437  
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DLD1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	250.1
2.5°	249.0
5°	246.4
7.5°	241.5
10°	235.1
12.5°	227.3
15°	217.9
17.5°	207.0
20°	195.4
22.5°	183.0
25°	170.6
27.5°	157.9
30°	144.8
32.5°	131.6
35°	117.0
37.5°	101.6
40°	87.0
42.5°	71.6
45°	56.6
47.5°	43.9
50°	30.8
52.5°	18.4
55°	13.9
57.5°	12.8
60°	11.6
62.5°	10.1
65°	9.0
67.5°	7.9
70°	6.8
72.5°	5.6
75°	4.9
77.5°	3.8
80°	3.0
82.5°	1.9
85°	1.1
87.5°	0.8
90°	0.0

(END OF REPORT)