

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296396

Luminaire Tested: P3AS13R30W2N902750DE010 E3DLD1LI_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296396
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30W2N902750DE010 E3DLD1LI_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 5000K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 628.0 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296396
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLD1LI_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296396

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLD1LI_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70			
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148365
5°	145036
10°	134867
15°	120001
20°	103212
25°	87441
30°	72593
35°	56938
40°	40819
45°	26762
50°	15249
55°	10016
60°	9473
65°	8821
70°	7886
75°	7202
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26762 cd/sqm



TEST NUMBER: P1296396

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLD1LI_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	9.7
10°-20°	147.0	23.4
20°-30°	165.6	26.4
30°-40°	132.3	21.1
40°-50°	68.0	10.8
50°-60°	25.6	4.1
60°-70°	16.8	2.7
70°-80°	9.0	1.4
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	373.7	59.5
0°-40°	506.0	80.6
0°-60°	599.6	95.5
0°-90°	628.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	628.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	677	
5°	659	61
15°	529	147
25°	361	166
35°	213	132
45°	86	68
55°	26	26
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296396

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLD1LI_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	676.6
1°	676.6
2°	674.3
3°	670.4
4°	665.0
5°	658.9
6°	651.2
7°	641.2
8°	630.4
9°	618.0
10°	605.7
11°	591.8
12°	577.2
13°	561.8
14°	545.6
15°	528.6
17.5°	485.5
20°	442.3
22.5°	400.7
25°	361.4
27.5°	322.9
30°	286.7
32.5°	249.7
35°	212.7
37.5°	176.5
40°	142.6
42.5°	112.5
45°	86.3
47.5°	64.0
50°	44.7
52.5°	31.6
55°	26.2
57.5°	23.9
60°	21.6
62.5°	19.3
65°	17.0
67.5°	14.6
70°	12.3
72.5°	10.0
75°	8.5
77.5°	6.9
80°	5.4
82.5°	3.9
85°	2.3
87.5°	0.8



TEST NUMBER: P1296396
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLD1LI_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)