

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296408

Luminaire Tested: P3AS13R30W2N902750DE010 E3DLD1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296408
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30W2N902750DE010 E3DLD1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 623.0 lumens
Efficiency: N/A
Efficacy: 50.6 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296408
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLD1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296408

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLD1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	84	80	78	76			76
4	94	85	79	74	92	84	79	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147181
5°	143869
10°	133798
15°	119047
20°	102396
25°	86739
30°	72011
35°	56483
40°	40476
45°	26545
50°	15113
55°	9940
60°	9385
65°	8717
70°	7822
75°	7117
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26545 cd/sqm



TEST NUMBER: P1296408

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLD1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.7	9.7
10°-20°	145.8	23.4
20°-30°	164.3	26.4
30°-40°	131.2	21.1
40°-50°	67.4	10.8
50°-60°	25.4	4.1
60°-70°	16.6	2.7
70°-80°	9.0	1.4
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.8	59.5
0°-40°	502.0	80.6
0°-60°	594.8	95.5
0°-90°	623.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	623.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	671	
5°	654	61
15°	524	146
25°	358	164
35°	211	131
45°	86	67
55°	26	25
65°	17	17
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1296408
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	671.2
1°	671.2
2°	668.9
3°	665.1
4°	659.7
5°	653.6
6°	646.0
7°	636.0
8°	625.3
9°	613.1
10°	600.9
11°	587.1
12°	572.6
13°	557.3
14°	541.3
15°	524.4
17.5°	481.6
20°	438.8
22.5°	397.5
25°	358.5
27.5°	320.3
30°	284.4
32.5°	247.7
35°	211.0
37.5°	175.1
40°	141.4
42.5°	111.6
45°	85.6
47.5°	63.5
50°	44.3
52.5°	31.3
55°	26.0
57.5°	23.7
60°	21.4
62.5°	19.1
65°	16.8
67.5°	14.5
70°	12.2
72.5°	9.9
75°	8.4
77.5°	6.9
80°	5.4
82.5°	3.8
85°	2.3
87.5°	0.8



TEST NUMBER: P1296408
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)