

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296415

Luminaire Tested: P3AS13R30W2N902750DE010 E3DLP1GPH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30W2N902750DE010 E3DLP1GPH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 245.0 lumens
Efficiency: N/A
Efficacy: 19.9 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296415
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLP1GPH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296415
 CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLP1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74	74	74	74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70	70	70	70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65	65	65	65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61	61	61	61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58	58	58	58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55	55	55	55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52	52	52	52

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83721
5°	81114
10°	73078
15°	60454
20°	46811
25°	35107
30°	25498
35°	16972
40°	10448
45°	6140
50°	3753
55°	3058
60°	2675
65°	2179
70°	1923
75°	1949
80°	1389
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6140 cd/sqm



TEST NUMBER: P1296415

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLP1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.9	13.8
10°-20°	73.3	29.9
20°-30°	66.7	27.2
30°-40°	40.3	16.5
40°-50°	16.2	6.6
50°-60°	7.2	2.9
60°-70°	4.3	1.8
70°-80°	2.4	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	174.0	71.0
0°-40°	214.3	87.5
0°-60°	237.6	97.0
0°-90°	245.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	245.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	382	
5°	368	34
15°	266	73
25°	145	67
35°	63	40
45°	20	16
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1296415
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	381.8
1°	381.4
2°	379.9
3°	377.2
4°	373.4
5°	368.5
6°	362.4
7°	356.0
8°	347.6
9°	338.1
10°	328.2
11°	316.8
12°	304.7
13°	292.5
14°	279.2
15°	266.3
17.5°	232.5
20°	200.6
22.5°	171.0
25°	145.1
27.5°	121.6
30°	100.7
32.5°	81.3
35°	63.4
37.5°	48.6
40°	36.5
42.5°	26.6
45°	19.8
47.5°	14.8
50°	11.0
52.5°	8.7
55°	8.0
57.5°	6.8
60°	6.1
62.5°	4.9
65°	4.2
67.5°	3.8
70°	3.0
72.5°	2.7
75°	2.3
77.5°	1.9
80°	1.1
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1296415
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3DLP1GPH_4000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)