

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298579

Luminaire Tested: P3AS13R65W2N902750DE010 E3DL1MW\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298579  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R65W2N902750DE010 E3DL1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,  
E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 767.0 lumens  
Efficiency: N/A  
Efficacy: 62.4 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298579  
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DL1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1298579

CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DL1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68	68	68	68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63	63	63	63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58	58	58	58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55	55	55	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48	48	48	48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	180885
5°	178714
10°	171918
15°	161045
20°	144866
25°	123007
30°	96217
35°	68556
40°	44855
45°	27724
50°	14089
55°	4970
60°	4342
65°	4358
70°	3911
75°	3897
80°	3915
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 27724 cd/sqm



TEST NUMBER: P1298579

CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DL1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	76.2	9.9
10°-20°	197.4	25.7
20°-30°	230.8	30.1
30°-40°	161.3	21.0
40°-50°	71.0	9.3
50°-60°	15.8	2.1
60°-70°	8.0	1.0
70°-80°	4.9	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	504.4	65.8
0°-40°	665.7	86.8
0°-60°	752.5	98.1
0°-90°	767.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	767.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	825	
5°	812	76
15°	709	197
25°	508	231
35°	256	161
45°	89	71
55°	13	16
65°	8	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1298579  
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DL1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	824.9
2.5°	821.8
5°	811.9
7.5°	795.1
10°	772.1
12.5°	743.8
15°	709.4
17.5°	667.4
20°	620.8
22.5°	568.0
25°	508.4
27.5°	445.7
30°	380.0
32.5°	316.5
35°	256.1
37.5°	203.4
40°	156.7
42.5°	118.5
45°	89.4
47.5°	65.7
50°	41.3
52.5°	21.4
55°	13.0
57.5°	11.5
60°	9.9
62.5°	9.2
65°	8.4
67.5°	6.9
70°	6.1
72.5°	5.4
75°	4.6
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)