

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296450

Luminaire Tested: P3AS13R30W2N902750DE010 E3PHLD1MW\_4000K

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296450  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R30W2N902750DE010 E3PHLD1MW\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 4000K CCT AND, 90CRI ,  
E3PHLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 603.1 lumens  
Efficiency: N/A  
Efficacy: 49.0 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296450  
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLD1MW\_4000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1296450

CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLD1MW\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 58.5   | 9.7       |
| 10°-20°   | 124.7  | 20.7      |
| 20°-30°   | 127.8  | 21.2      |
| 30°-40°   | 104.5  | 17.3      |
| 40°-50°   | 78.2   | 13.0      |
| 50°-60°   | 54.9   | 9.1       |
| 60°-70°   | 34.6   | 5.7       |
| 70°-80°   | 16.6   | 2.8       |
| 80°-90°   | 3.2    | 0.5       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 311.1  | 51.6      |
| 0°-40°    | 415.6  | 68.9      |
| 0°-60°    | 548.6  | 91.0      |
| 0°-90°    | 603.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 603.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 678 |      |
| 5°  | 645 | 58   |
| 15° | 447 | 125  |
| 25° | 277 | 128  |
| 35° | 166 | 105  |
| 45° | 101 | 78   |
| 55° | 60  | 55   |
| 65° | 35  | 35   |
| 75° | 16  | 17   |
| 85° | 2   | 3    |
| 90° | 0   |      |



TEST NUMBER: P1296450  
CATALOG NUMBER: P3AS13R30W2N902750DE010 E3PHLD1MW\_4000K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 677.6 |
| 2.5°  | 670.9 |
| 5°    | 645.2 |
| 7.5°  | 602.7 |
| 10°   | 550.1 |
| 12.5° | 498.7 |
| 15°   | 447.3 |
| 17.5° | 400.3 |
| 20°   | 356.7 |
| 22.5° | 315.3 |
| 25°   | 277.3 |
| 27.5° | 243.8 |
| 30°   | 213.6 |
| 32.5° | 189.0 |
| 35°   | 165.5 |
| 37.5° | 146.5 |
| 40°   | 128.6 |
| 42.5° | 114.1 |
| 45°   | 100.6 |
| 47.5° | 88.3  |
| 50°   | 78.3  |
| 52.5° | 69.3  |
| 55°   | 60.4  |
| 57.5° | 53.7  |
| 60°   | 47.0  |
| 62.5° | 40.3  |
| 65°   | 34.7  |
| 67.5° | 29.1  |
| 70°   | 24.6  |
| 72.5° | 20.1  |
| 75°   | 15.7  |
| 77.5° | 11.2  |
| 80°   | 7.8   |
| 82.5° | 4.5   |
| 85°   | 2.2   |
| 87.5° | 1.1   |
| 90°   | 0.0   |

(END OF REPORT)