

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298609

Luminaire Tested: P3AS13R65W2N902750DE010 E3DLD1MW\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298609  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R65W2N902750DE010 E3DLD1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,  
E3DLD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 602.0 lumens  
Efficiency: N/A  
Efficacy: 48.9 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298609  
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLD1MW\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1298609  
 CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLD1MW\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	107119
5°	105679
10°	102136
15°	96323
20°	88838
25°	80642
30°	71429
35°	60793
40°	48376
45°	34143
50°	19820
55°	10819
60°	10043
65°	9132
70°	8335
75°	7795
80°	6819
85°	5787

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 34143 cd/sqm



TEST NUMBER: P1298609

CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLD1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.2	7.5
10°-20°	118.7	19.7
20°-30°	152.5	25.3
30°-40°	141.1	23.4
40°-50°	85.2	14.2
50°-60°	29.1	4.8
60°-70°	17.5	2.9
70°-80°	9.9	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	316.4	52.6
0°-40°	457.6	76.0
0°-60°	571.8	95.0
0°-90°	602.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	602.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	488	
5°	480	45
15°	424	119
25°	333	153
35°	227	141
45°	110	85
55°	28	29
65°	18	17
75°	9	10
85°	2	3
90°	0	



TEST NUMBER: P1298609  
CATALOG NUMBER: P3AS13R65W2N902750DE010 E3DLD1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	488.5
2.5°	486.3
5°	480.1
7.5°	471.0
10°	458.7
12.5°	443.4
15°	424.3
17.5°	403.7
20°	380.7
22.5°	357.0
25°	333.3
27.5°	308.1
30°	282.1
32.5°	256.1
35°	227.1
37.5°	198.8
40°	169.0
42.5°	139.1
45°	110.1
47.5°	83.3
50°	58.1
52.5°	36.7
55°	28.3
57.5°	25.2
60°	22.9
62.5°	19.9
65°	17.6
67.5°	15.3
70°	13.0
72.5°	11.5
75°	9.2
77.5°	7.6
80°	5.4
82.5°	3.8
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)