

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296531

Luminaire Tested: P3AS13R30W2N902765DE010 E3DL1H\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296531  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R30W2N902765DE010 E3DL1H\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3500K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 821.0 lumens  
Efficiency: N/A  
Efficacy: 66.7 lumens/watt  
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296531  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DL1H\_3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296531  
 CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DL1H\_3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20					
RC	80				70				50				30				10			0		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	97	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	93	92	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	91	89	87	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	88	85	83	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	86	83	81	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	85	82	79	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	81	78	76	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	78	75	73	71	76	72	70	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	73	70	67	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	73	70	67	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	71	67	65	63

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	479084
5°	455975
10°	383538
15°	276596
20°	171562
25°	97578
30°	54211
35°	29473
40°	15543
45°	8404
50°	4503
55°	2982
60°	2719
65°	2802
70°	2500
75°	1949
80°	2020
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8404 cd/sqm



TEST NUMBER: P1296531

CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DL1H\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	186.5	22.7
10°-20°	331.6	40.4
20°-30°	191.6	23.3
30°-40°	72.7	8.9
40°-50°	22.3	2.7
50°-60°	7.5	0.9
60°-70°	5.1	0.6
70°-80°	2.8	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	709.7	86.4
0°-40°	782.5	95.3
0°-60°	812.3	98.9
0°-90°	821.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	821.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2185	
5°	2072	187
15°	1218	332
25°	403	192
35°	110	73
45°	27	22
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1296531  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DL1H\_3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2184.8
1°	2183.2
2°	2170.0
3°	2145.2
4°	2114.2
5°	2071.5
6°	2017.3
7°	1956.8
8°	1889.3
9°	1808.6
10°	1722.5
11°	1629.5
12°	1531.0
13°	1427.8
14°	1323.1
15°	1218.4
17.5°	960.9
20°	735.2
22.5°	545.2
25°	403.3
27.5°	293.2
30°	214.1
32.5°	154.3
35°	110.1
37.5°	76.8
40°	54.3
42.5°	38.0
45°	27.1
47.5°	18.6
50°	13.2
52.5°	9.3
55°	7.8
57.5°	7.0
60°	6.2
62.5°	5.4
65°	5.4
67.5°	4.7
70°	3.9
72.5°	3.1
75°	2.3
77.5°	2.3
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.0



TEST NUMBER: P1296531  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DL1H\_3500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)