

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296577

Luminaire Tested: P3AS13R30W2N902765DE010 E3DLD1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R30W2N902765DE010 E3DLD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 565.0 lumens
Efficiency: N/A
Efficacy: 45.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296577
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1296577

CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.0	9.7
10°-20°	132.2	23.4
20°-30°	149.0	26.4
30°-40°	119.0	21.1
40°-50°	61.2	10.8
50°-60°	23.0	4.1
60°-70°	15.1	2.7
70°-80°	8.1	1.4
80°-90°	2.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	336.3	59.5
0°-40°	455.3	80.6
0°-60°	539.4	95.5
0°-90°	565.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	565.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	609	
5°	593	55
15°	476	132
25°	325	149
35°	191	119
45°	78	61
55°	24	23
65°	15	15
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1296577
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	608.7
1°	608.7
2°	606.6
3°	603.2
4°	598.3
5°	592.8
6°	585.8
7°	576.8
8°	567.1
9°	556.0
10°	544.9
11°	532.5
12°	519.3
13°	505.4
14°	490.9
15°	475.6
17.5°	436.8
20°	398.0
22.5°	360.5
25°	325.2
27.5°	290.5
30°	257.9
32.5°	224.6
35°	191.4
37.5°	158.8
40°	128.3
42.5°	101.2
45°	77.7
47.5°	57.5
50°	40.2
52.5°	28.4
55°	23.6
57.5°	21.5
60°	19.4
62.5°	17.3
65°	15.3
67.5°	13.2
70°	11.1
72.5°	9.0
75°	7.6
77.5°	6.2
80°	4.9
82.5°	3.5
85°	2.1
87.5°	0.7



TEST NUMBER: P1296577
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLD1MW_2700K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)