

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296600

Luminaire Tested: P3AS13R30W2N902765DE010 E3DLP1GPH\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296600  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R30W2N902765DE010 E3DLP1GPH\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 6500K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 244.0 lumens  
Efficiency: N/A  
Efficacy: 19.8 lumens/watt  
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296600  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLP1GPH\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296600  
 CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLP1GPH\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86
3	102	95	90	86	100	94	89	85	91	87	84	89	86	83	87	84	82	80			80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			74
5	92	84	78	73	90	83	77	73	81	76	72	79	75	72	78	74	71	70			70
6	88	79	73	68	86	78	72	68	76	71	68	75	71	67	74	70	67	65			65
7	83	74	68	64	82	74	68	64	72	67	63	71	67	63	70	66	63	61			61
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			58
9	76	67	61	57	75	66	60	57	65	60	56	64	60	56	63	59	56	55			55
10	73	63	58	54	72	63	57	54	62	57	53	61	57	53	60	56	53	52			52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	83371
5°	80783
10°	72789
15°	60205
20°	46624
25°	34962
30°	25396
35°	16918
40°	10391
45°	6109
50°	3753
55°	3020
60°	2675
65°	2179
70°	1923
75°	1949
80°	1389
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6109 cd/sqm



TEST NUMBER: P1296600

CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLP1GPH\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	33.8	13.8
10°-20°	73.0	29.9
20°-30°	66.5	27.2
30°-40°	40.2	16.5
40°-50°	16.1	6.6
50°-60°	7.1	2.9
60°-70°	4.3	1.8
70°-80°	2.3	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.3	71.0
0°-40°	213.4	87.5
0°-60°	236.7	97.0
0°-90°	244.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	244.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	380	
5°	367	34
15°	265	73
25°	144	66
35°	63	40
45°	20	16
55°	8	7
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1296600  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLP1GPH\_6500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	380.2
1°	379.9
2°	378.3
3°	375.7
4°	371.9
5°	367.0
6°	360.9
7°	354.5
8°	346.2
9°	336.7
10°	326.9
11°	315.5
12°	303.4
13°	291.3
14°	278.1
15°	265.2
17.5°	231.5
20°	199.8
22.5°	170.3
25°	144.5
27.5°	121.1
30°	100.3
32.5°	81.0
35°	63.2
37.5°	48.4
40°	36.3
42.5°	26.5
45°	19.7
47.5°	14.8
50°	11.0
52.5°	8.7
55°	7.9
57.5°	6.8
60°	6.1
62.5°	4.9
65°	4.2
67.5°	3.8
70°	3.0
72.5°	2.6
75°	2.3
77.5°	1.9
80°	1.1
82.5°	0.8
85°	0.8
87.5°	0.4



TEST NUMBER: P1296600  
CATALOG NUMBER: P3AS13R30W2N902765DE010 E3DLP1GPH\_6500K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)