

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296716

Luminaire Tested: P3AS13R35W2N902750DE010 E3DLD1GPH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296716
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35W2N902750DE010 E3DLD1GPH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3500K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 308.0 lumens
Efficiency: N/A
Efficacy: 25.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296716
CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DLD1GPH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1296716
 CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DLD1GPH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	70367
5°	68875
10°	64483
15°	57889
20°	50358
25°	42922
30°	35955
35°	28643
40°	20696
45°	13087
50°	7130
55°	4932
60°	4693
65°	4358
70°	4167
75°	3558
80°	3410
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13087 cd/sqm



TEST NUMBER: P1296716

CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DLD1GPH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.1	9.5
10°-20°	71.0	23.0
20°-30°	81.3	26.4
30°-40°	66.4	21.6
40°-50°	33.4	10.9
50°-60°	12.4	4.0
60°-70°	8.3	2.7
70°-80°	4.6	1.5
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	181.4	58.9
0°-40°	247.8	80.5
0°-60°	293.6	95.3
0°-90°	308.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	308.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	321	
5°	313	29
15°	255	71
25°	177	81
35°	107	66
45°	42	33
55°	13	12
65°	8	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1296716
CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	320.9
1°	320.5
2°	319.7
3°	318.2
4°	315.9
5°	312.9
6°	309.1
7°	305.2
8°	300.3
9°	295.4
10°	289.6
11°	283.6
12°	277.1
13°	269.8
14°	262.2
15°	255.0
17.5°	235.6
20°	215.8
22.5°	195.6
25°	177.4
27.5°	159.5
30°	142.0
32.5°	124.5
35°	107.0
37.5°	89.4
40°	72.3
42.5°	56.3
45°	42.2
47.5°	30.4
50°	20.9
52.5°	15.2
55°	12.9
57.5°	11.8
60°	10.7
62.5°	9.5
65°	8.4
67.5°	7.2
70°	6.5
72.5°	5.3
75°	4.2
77.5°	3.4
80°	2.7
82.5°	1.9
85°	1.1
87.5°	0.8



TEST NUMBER: P1296716
CATALOG NUMBER: P3AS13R35W2N902750DE010 E3DLD1GPH_3500K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)