

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298891

Luminaire Tested: P3AS13R70W2N902750DE010 E3DL1H\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298891  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R70W2N902750DE010 E3DL1H\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 776.9 lumens  
Efficiency: N/A  
Efficacy: 63.2 lumens/watt  
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298891  
CATALOG NUMBER: P3AS13R70W2N902750DE010 E3DL1H\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1298891  
 CATALOG NUMBER: P3AS13R70W2N902750DE010 E3DL1H\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.6	8.2
10°-20°	170.4	21.9
20°-30°	221.4	28.5
30°-40°	187.9	24.2
40°-50°	96.9	12.5
50°-60°	18.7	2.4
60°-70°	10.1	1.3
70°-80°	6.2	0.8
80°-90°	1.8	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	455.4	58.6
0°-40°	643.3	82.8
0°-60°	758.8	97.7
0°-90°	776.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	776.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	686	
5°	675	64
15°	609	170
25°	486	221
35°	302	188
45°	125	97
55°	15	19
65°	10	10
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1298891  
CATALOG NUMBER: P3AS13R70W2N902750DE010 E3DL1H\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	686.0
2.5°	683.7
5°	675.2
7.5°	662.8
10°	648.2
12.5°	629.6
15°	608.8
17.5°	583.3
20°	554.8
22.5°	522.4
25°	486.1
27.5°	445.2
30°	401.2
32.5°	352.6
35°	302.5
37.5°	253.1
40°	206.0
42.5°	162.0
45°	125.0
47.5°	91.8
50°	53.2
52.5°	23.1
55°	14.7
57.5°	13.9
60°	12.3
62.5°	11.6
65°	10.0
67.5°	9.3
70°	7.7
72.5°	6.9
75°	6.2
77.5°	4.6
80°	3.9
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)