

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298928

Luminaire Tested: P3AS13R70W2N902750DE010 E3DLP1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298928
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R70W2N902750DE010 E3DLP1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 549.0 lumens
Efficiency: N/A
Efficacy: 44.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298928
CATALOG NUMBER: P3AS13R70W2N902750DE010 E3DLP1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298928
 CATALOG NUMBER: P3AS13R70W2N902750DE010 E3DLP1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94		92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86		84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79		77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73		71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67		65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62		61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58		56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54		52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50		49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47		46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	128784
5°	126414
10°	119192
15°	108173
20°	94625
25°	79819
30°	65352
35°	50701
40°	36297
45°	22979
50°	11462
55°	6996
60°	6008
65°	5552
70°	4873
75°	4490
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22979 cd/sqm



TEST NUMBER: P1298928

CATALOG NUMBER: P3AS13R70W2N902750DE010 E3DLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.6	9.8
10°-20°	132.6	24.2
20°-30°	151.0	27.5
30°-40°	118.1	21.5
40°-50°	58.0	10.6
50°-60°	17.8	3.2
60°-70°	10.6	1.9
70°-80°	5.6	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	337.2	61.4
0°-40°	455.3	82.9
0°-60°	531.1	96.7
0°-90°	549.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	549.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	587	
5°	574	54
15°	476	133
25°	330	151
35°	189	118
45°	74	58
55°	18	18
65°	11	11
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1298928
CATALOG NUMBER: P3AS13R70W2N902750DE010 E3DLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	587.3
2.5°	584.2
5°	574.3
7.5°	558.2
10°	535.3
12.5°	508.6
15°	476.5
17.5°	442.2
20°	405.5
22.5°	367.3
25°	329.9
27.5°	293.2
30°	258.1
32.5°	223.0
35°	189.4
37.5°	157.3
40°	126.8
42.5°	98.5
45°	74.1
47.5°	51.9
50°	33.6
52.5°	22.1
55°	18.3
57.5°	16.0
60°	13.7
62.5°	12.2
65°	10.7
67.5°	9.2
70°	7.6
72.5°	6.1
75°	5.3
77.5°	4.6
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)