

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296838

Luminaire Tested: P3AS13R35W2N902765DE010 E3DL1H\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1296838  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R35W2N902765DE010 E3DL1H\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,  
E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 803.0 lumens  
Efficiency: N/A  
Efficacy: 65.3 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296838  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DL1H\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296838  
 CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DL1H\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	80	80	80	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	70	70	70	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66	66	66	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	68	65	64	64	64	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	61	61	61	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	404989
5°	389235
10°	339139
15°	259752
20°	173778
25°	105151
30°	60338
35°	33729
40°	17919
45°	9241
50°	4435
55°	3517
60°	3333
65°	2750
70°	2949
75°	2626
80°	2904
85°	2013

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9241 cd/sqm



TEST NUMBER: P1296838

CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DL1H\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.9	20.0
10°-20°	311.8	38.8
20°-30°	204.1	25.4
30°-40°	82.8	10.3
40°-50°	24.8	3.1
50°-60°	8.4	1.1
60°-70°	5.7	0.7
70°-80°	3.3	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	676.8	84.3
0°-40°	759.6	94.6
0°-60°	792.9	98.7
0°-90°	803.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1847	
5°	1768	161
15°	1144	312
25°	435	204
35°	126	83
45°	30	25
55°	9	8
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1296838  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DL1H\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1846.9
1°	1843.9
2°	1835.5
3°	1818.7
4°	1798.8
5°	1768.3
6°	1730.1
7°	1687.3
8°	1639.2
9°	1584.2
10°	1523.1
11°	1455.1
12°	1384.1
13°	1304.6
14°	1229.0
15°	1144.2
17.5°	938.7
20°	744.7
22.5°	572.9
25°	434.6
27.5°	323.9
30°	238.3
32.5°	174.9
35°	126.0
37.5°	89.4
40°	62.6
42.5°	43.5
45°	29.8
47.5°	19.9
50°	13.0
52.5°	9.9
55°	9.2
57.5°	8.4
60°	7.6
62.5°	6.9
65°	5.3
67.5°	4.6
70°	4.6
72.5°	3.8
75°	3.1
77.5°	2.3
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8



TEST NUMBER: P1296838  
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DL1H\_3000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)