

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296862

Luminaire Tested: P3AS13R35W2N902765DE010 E3DL1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296862
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R35W2N902765DE010 E3DL1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 803.0 lumens
Efficiency: N/A
Efficacy: 65.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296862
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DL1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296862

CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DL1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.9	20.0
10°-20°	311.8	38.8
20°-30°	204.1	25.4
30°-40°	82.8	10.3
40°-50°	24.8	3.1
50°-60°	8.4	1.1
60°-70°	5.7	0.7
70°-80°	3.3	0.4
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	676.8	84.3
0°-40°	759.6	94.6
0°-60°	792.9	98.7
0°-90°	803.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	803.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1847	
5°	1768	161
15°	1144	312
25°	435	204
35°	126	83
45°	30	25
55°	9	8
65°	5	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1296862
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1846.9
1°	1843.9
2°	1835.5
3°	1818.7
4°	1798.8
5°	1768.3
6°	1730.1
7°	1687.3
8°	1639.2
9°	1584.2
10°	1523.1
11°	1455.1
12°	1384.1
13°	1304.6
14°	1229.0
15°	1144.2
17.5°	938.7
20°	744.7
22.5°	572.9
25°	434.6
27.5°	323.9
30°	238.3
32.5°	174.9
35°	126.0
37.5°	89.4
40°	62.6
42.5°	43.5
45°	29.8
47.5°	19.9
50°	13.0
52.5°	9.9
55°	9.2
57.5°	8.4
60°	7.6
62.5°	6.9
65°	5.3
67.5°	4.6
70°	4.6
72.5°	3.8
75°	3.1
77.5°	2.3
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8



TEST NUMBER: P1296862
CATALOG NUMBER: P3AS13R35W2N902765DE010 E3DL1WMH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)