

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299054

Luminaire Tested: P3AS13R70W2N902765DE010 E3DLP1GPH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299054  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R70W2N902765DE010 E3DLP1GPH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 244.0 lumens  
Efficiency: N/A  
Efficacy: 19.8 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299054  
CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1GPH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299054  
 CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1GPH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	57232
5°	56174
10°	52972
15°	48082
20°	42050
25°	35470
30°	29042
35°	22540
40°	16116
45°	10203
50°	5083
55°	3097
60°	2675
65°	2491
70°	2180
75°	2033
80°	1768
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 10203 cd/sqm



TEST NUMBER: P1299054

CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1GPH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	23.8	9.8
10°-20°	58.9	24.2
20°-30°	67.1	27.5
30°-40°	52.5	21.5
40°-50°	25.8	10.6
50°-60°	7.9	3.2
60°-70°	4.7	1.9
70°-80°	2.5	1.0
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.9	61.4
0°-40°	202.3	82.9
0°-60°	236.0	96.7
0°-90°	244.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	244.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	261	
5°	255	24
15°	212	59
25°	147	67
35°	84	52
45°	33	26
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1299054  
CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1GPH\_2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	261.0
2.5°	259.6
5°	255.2
7.5°	248.1
10°	237.9
12.5°	226.0
15°	211.8
17.5°	196.5
20°	180.2
22.5°	163.3
25°	146.6
27.5°	130.3
30°	114.7
32.5°	99.1
35°	84.2
37.5°	69.9
40°	56.3
42.5°	43.8
45°	32.9
47.5°	23.1
50°	14.9
52.5°	9.8
55°	8.1
57.5°	7.1
60°	6.1
62.5°	5.4
65°	4.8
67.5°	4.1
70°	3.4
72.5°	2.7
75°	2.4
77.5°	2.0
80°	1.4
82.5°	1.0
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)