

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299058

Luminaire Tested: P3AS13R70W2N902765DE010 E3DLP1GPH\_5000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299058  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R70W2N902765DE010 E3DLP1GPH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 90CRI ,  
E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 272.0 lumens  
Efficiency: N/A  
Efficacy: 22.1 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299058  
CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1GPH\_5000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1299058

CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1GPH\_5000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	26.6	9.8
10°-20°	65.7	24.2
20°-30°	74.8	27.5
30°-40°	58.5	21.5
40°-50°	28.7	10.6
50°-60°	8.8	3.2
60°-70°	5.2	1.9
70°-80°	2.8	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	167.1	61.4
0°-40°	225.6	82.9
0°-60°	263.1	96.7
0°-90°	272.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	272.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	291	
5°	284	27
15°	236	66
25°	163	75
35°	94	58
45°	37	29
55°	9	9
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1299058  
CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1GPH\_5000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	291.0
2.5°	289.4
5°	284.5
7.5°	276.6
10°	265.2
12.5°	252.0
15°	236.1
17.5°	219.1
20°	200.9
22.5°	182.0
25°	163.4
27.5°	145.3
30°	127.9
32.5°	110.5
35°	93.8
37.5°	77.9
40°	62.8
42.5°	48.8
45°	36.7
47.5°	25.7
50°	16.6
52.5°	11.0
55°	9.1
57.5°	7.9
60°	6.8
62.5°	6.1
65°	5.3
67.5°	4.5
70°	3.8
72.5°	3.0
75°	2.6
77.5°	2.3
80°	1.5
82.5°	1.1
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)