

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1299067

Luminaire Tested: P3AS13R70W2N902765DE010 E3DLP1LI\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1299067  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R70W2N902765DE010 E3DLP1LI\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,  
E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 549.0 lumens  
Efficiency: N/A  
Efficacy: 44.6 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1299067  
CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1LI\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1299067

CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1LI\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92			92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84			84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77			77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71			71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61			61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56			56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46			46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	128784
5°	126414
10°	119192
15°	108173
20°	94625
25°	79819
30°	65352
35°	50701
40°	36297
45°	22979
50°	11462
55°	6996
60°	6008
65°	5552
70°	4873
75°	4490
80°	3915
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 22979 cd/sqm



TEST NUMBER: P1299067

CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1LI\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.6	9.8
10°-20°	132.6	24.2
20°-30°	151.0	27.5
30°-40°	118.1	21.5
40°-50°	58.0	10.6
50°-60°	17.8	3.2
60°-70°	10.6	1.9
70°-80°	5.6	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	337.2	61.4
0°-40°	455.3	82.9
0°-60°	531.1	96.7
0°-90°	549.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	549.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	587	
5°	574	54
15°	476	133
25°	330	151
35°	189	118
45°	74	58
55°	18	18
65°	11	11
75°	5	6
85°	2	2
90°	0	



TEST NUMBER: P1299067  
CATALOG NUMBER: P3AS13R70W2N902765DE010 E3DLP1LI\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	587.3
2.5°	584.2
5°	574.3
7.5°	558.2
10°	535.3
12.5°	508.6
15°	476.5
17.5°	442.2
20°	405.5
22.5°	367.3
25°	329.9
27.5°	293.2
30°	258.1
32.5°	223.0
35°	189.4
37.5°	157.3
40°	126.8
42.5°	98.5
45°	74.1
47.5°	51.9
50°	33.6
52.5°	22.1
55°	18.3
57.5°	16.0
60°	13.7
62.5°	12.2
65°	10.7
67.5°	9.2
70°	7.6
72.5°	6.1
75°	5.3
77.5°	4.6
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)